

Pressure Controls Compatible with R-410A

	PRODUCT	SWITCH ACTION	BOTTOM OF RANGE	TOP OF RANGE	MAXIMUM WORKING PRESSURE	TYPICAL APPLICATIONS
P70 SERIES ADJUSTABLE ON/OFF PRESSURE CONTROLS	P70AA-2C	SPST Open Low	0	150	325	Suction pressure control – loss of charge
	P70AA-400C	SPST Open Low	100	470	690	Fan cycling for head pressure control
	P70CA-400C	SPST Open High	200	610	690	High pressure compressor shutdown – Auto Reset
	P70DA-400C	SPST Open High	200	610	690	High pressure compressor shutdown – Manual Reset
P170 SERIES ADJUSTABLE ON/OFF PRESSURE CONTROLS	P170AA-2C	SPST Open Low	0	150	325	Suction pressure control – loss of charge
	P170AA-400C	SPST Open Low	100	470	690	Fan cycling for head pressure control
	P170CA-400C	SPST Open High	200	610	690	High pressure compressor shutdown – Auto Reset
	P170DA-400C	SPST Open High	200	610	690	High pressure compressor shutdown – Manual Reset
P100 SERIES NON- ADJUSTABLE ON/OFF PRESSURE SWITCHES	P100AP-332C	SPST Open Low	300	400	600	Fan cycling for head pressure control
	P100AP-201C	SPST Open Low	10	32	600	Low pressure switch – loss of charge Compressor cycling Auto Reset
	P100DA-81C/D ¹	SPST Open High	Manual Reset	630	800	High pressure compressor shutdown – Manual Reset
	P100DA-86D ³	SPST Open High	Manual Reset	575	800	High pressure compressor shutdown – Manual Reset
	P100CP-85D ²	SPST Open High	565	665	800	High pressure compressor shutdown – Auto Reset
	P100CE-11D ¹	SPST Open High HD Contacts	450	550	800	High pressure compressor shutdown – Auto Reset
P266 SERIES ADJUSTABLE MODULATING ELECTRONIC FAN SPEED CONTROLS	P266Axx ³	Modulating	30	720	765	Head pressure control 208/230/240 V
	P266Bxx ³	Modulating	30	720	765	Head pressure control 460/480/575 V



1. Bulk Pack Only. 50 per box. Minimum order 250.
2. Bulk Pack Only. 50 per box. Minimum order 100.
3. R-410A compatibility offered with P266SNR-2K transducer