

Applied Chiller Parts

Applied Equipment YORK[®] Genuine Parts Catalog

Baldor Motors



YORK[®] equipment deserves YORK[®] parts.

Chiller/Cooling Tower Motors, Three Phase, TEAO, with Internal Aegis Bearing Protection Ring

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
024 42910 022	ECTM3611T-G-AO	3HP Motor with TEAO Enclosure (230/380-415V-3PH-60Hz)	TEAO	184	1800
024 42910 023	ECTM3704T-G-AO	3HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	213T	1200
024 42910 024	ECTM3615T-G-AO	5HP Motor with TEAO Enclosure (230/380-415V-3PH-60Hz)	TEAO	184T	1800
024 42910 025	ECTM3665T-G-AO	5HP Motor with TEAO Enclosure (208-230/460V-3PH-60Hz)	TEAO	184T	1800
024 42910 026	ECTM3708T-G-AO	5HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	213T	1200
024 42910 027	ECTM3768T-G-AO	5HP Motor with TEAO Enclosure (208-230/460V-3PH-60Hz)	TEAO	215T	1200
024 42910 028	ECTM3770T-G-AO	5HP Motor with TEAO Enclosure (208-230/460V-3PH-60Hz)	TEAO	213T	1800
024 42910 029	ECTM2276T-G-AO	5HP Motor with TEAO Enclosure (208-230/460V-3PH-60Hz)	TEAO	254T	1200
024 42910 030	ECTM3774T-G-AO	10HP Motor with TEAO Enclosure (208-230/460V-3PH-60Hz)	TEAO	215T	1800
024 42910 031	ECTM2332T-G-AO	10HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	256T	1200
024 42910 032	ECTM2333T-G-AO	15HP Motor with TEAO Enclosure (208-230/460V-3PH-60Hz)	TEAO	254T	1800
024 42910 033	ECTM4100T-G-AO	15HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	284T	1200
024 42910 034	ECTM2334T-G-AO	20HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	256T	1800
024 42910 035	ECTM4103T-G-AO	25HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	284T	1800
024 42910 036	ECTM4104T-G-AO	30HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	286T	1800
024 42910 037	ECTM4110T-G-AO	40HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	324T	1800
024 42910 038	ECTM4115T-G-AO	50HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	326T	1800
024 42910 039	ECTM4314T-G-AO	60HP Motor with TEAO Enclosure (230/460V-3PH-60Hz)	TEAO	364T	1800

Chiller/Cooling Tower Motors, Three Phase, TEFC, with Internal Aegis Bearing Protection Ring

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
024 42910 000	ECTM3661T-G	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	182T	1800
024 42910 001	ECTM3764T-G	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213T	1200
024 42910 002	ECTM3665T-G	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184T	1800
024 42910 003	ECTM3768T-G	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215T	1200
024 42910 004	ECTM3770T-G	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213T	1800
024 42910 005	ECTM2276T-G	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254T	1200
024 42910 006	ECTM3774T-G	10HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215T	1800
024 42910 007	ECTM2332T-G	10HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	256T	1200
024 42910 008	ECTM2333T-G	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254T	1800
024 42910 009	ECTM4100T-G	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	284T	1200
024 42910 010	ECTM2334T-G	20HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	256T	1800
024 42910 011	ECTM4102T-G	20HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	286T	1200
024 42910 012	ECTM4103T-G	25HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	284T	1800
024 42910 013	ECTM4111T-G	25HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	324T	1200
024 42910 014	ECTM4104T-G	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	286T	1800
024 42910 015	ECTM4117T-G	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	326T	1200
024 42910 016	ECTM4110T-G	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	324T	1800
024 42910 017	ECTM4308T-G	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	364T	1200
024 42910 018	ECTM4115T-G	50HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	326T	1800
024 42910 019	ECTM4312T-G	50HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	365T	1200
024 42910 020	ECTM4314T-G	60HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	364T	1800
024 42910 021	ECTM4403T-G	60HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	404T	1800

Close-Coupled Pump, Three Phase, ODP, Foot Mounted

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04222 003	EJMM3116T	1HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	143JM	1800
027 04222 005	EJMM3120T	1.5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	143JM	3600
027 04222 006	EJMM3154T	1.5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	145JM	1800
027 04222 009	EJMM3157T	2HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	145JM	1800
027 04222 008	EJMM3155T	2HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	145JM	3600
027 04222 011	EJMM3158T	3HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	145JM	3600
027 04222 013	EJMM3211T	3HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	182JM	1800
027 04222 016	EJMM3212T	5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	182JM	3600
027 04222 020	EJMM3218T	5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	184JM	1800
027 04222 021	EJMM3309T	5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215JM	1200
027 04222 022	EJMM3219T	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184JM	3600
027 04222 025	EJMM3311T	7.5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	213JM	1800
027 04222 028	EJMM2506T	7.5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	254JM	1200
027 04222 029	EJMM3312T	10HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213JM	3600
027 04222 033	EJMM3313T	10HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215JM	1800
027 04222 035	EJMM2511T	10HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	256JM	1200
027 04222 037	EJMM3314T	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215JM	3600
027 04222 039	EJMM2513T	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	254JM	1800
027 04222 041	EJMM2524T	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	284JM	1200
027 04222 042	EJMM2514T	20HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	254JM	3600
027 04222 043	EJMM2515T	20HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	354JM	1800
027 04222 044	EJMM2516T	25HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	256JM	3600
027 04222 045	EJMM2531T	25HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	284JM	1800
027 04222 046	EJMM2534T	30HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	284JM	3600
027 04222 047	EJMM2535T	30HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	286JM	1800
027 04222 048	EJMM2538T	40HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	286JM	3600
027 04222 049	EJMM2539T	40HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	324JM	1800
027 04222 050	EJMM2542T	50HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	324JM	3600
027 04222 051	EJMM2543T	50HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	326JM	1800
027 04222 052	EJMM2546T	60HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	326JM	3600



Close-Coupled Pump, Three Phase, ODP, Foot Mounted, with internal Aegis Bearing Protection Ring

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04222 004	EJMM3116T-G	1HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	143JM	1800
027 04222 007	EJMM3154T-G	1.5HP Motor with OBSP Enclosure (230/460V-3PH-60Hz)	OPSB	145JM	1800
027 04222 010	EJMM3157T-G	2HP Motor with OBSP Enclosure (230/460V-3PH-60Hz)	OBSP	145JM	1800
027 04222 012	EJMM3158T-G	3HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	145JM	3600
027 04222 014	EJMM3211T-G	3HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	182JM	1800
027 04222 017	EJMM3212T-G	5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	182JM	3600
027 04222 019	EJMM3218T-G	5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	184JM	1800
027 04222 023	EJMM3219T-G	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184JM	3600
027 04222 027	EJMM3311T-G	7.5HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	213JM	1800
027 04222 031	EJMM3312T-G	10HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213JM	3600
027 04222 034	EJMM3313T-G	10HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215JM	1800
027 04222 038	EJMM3314T-G	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215JM	3600
027 04222 040	EJMM2513T-G	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	254JM	1800



Close-Coupled Pump, Three Phase, TEFC

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04222 054	EJMM3546T	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	143JM	1800
027 04222 063	EJMM3554T	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	143JM	1800
027 04222 059	EJMM3550T	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	143JM	3600
027 04222 070	EJMM3558T	2HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145JM	1800
027 04222 067	EJMM3555T	2HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145JM	3600
027 04222 075	EJMM3559T	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145JM	3600
027 04222 080	EJMM3611T	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	182JM	1800
027 04222 077	EJMM3610T	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	182JM	3600
027 04222 086	EJMM3615T	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184JM	1800
027 04222 083	EJMM3613T	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184JM	3600
027 04222 089	EJMM3616T	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184JM	3600
027 04222 093	EJMM3710T	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213JM	1800
027 04222 091	EJMM3709T	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	213JM	3600
027 04222 099	EJMM3714T	10HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215JM	1800
027 04222 096	EJMM3711T	10HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215JM	3600
027 04222 108	EJMM3713T	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215JM	3600
027 04222 105	EJMM2333T	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254JM	1800
027 04222 103	EJMM2394T	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254JM	3600
027 04222 112	EJMM2334T	20HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	256JM	1800
027 04222 110	EJMM4106T	20HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	256JM	3600
027 04222 115	EJMM4103T	25HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	284JM	1800
027 04222 114	EJMM4107T	25HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	284JM	3600
027 04222 117	EJMM4104T	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	286JM	1800
027 04222 116	EJMM4108T	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	286JM	3600
027 04222 119	EJMM4110T	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	324JM	1800
027 04222 118	EJMM4109T	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	324JM	3600
027 04222 121	EJMM4115T	50HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	326JM	1800
027 04222 120	EJMM4114T	50HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	326JM	3600



Close-Coupled Pump, Three Phase, TEFC, Foot Mounted, with internal Aegis Bearing Protection Ring

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04222 056	EJMM3546T-G	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	143JM	1800
027 04222 065	EJMM3554T-G	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	143JM	1800
027 04222 061	EJMM3550T-G	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	143JM	3600
027 04222 072	EJMM3558T-G	2HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145JM	1800
027 04222 069	EJMM3555T-G	2HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145JM	3600
027 04222 082	EJMM3611T-G	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	182JM	1800
027 04222 078	EJMM3610T-G	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	182JM	3600
027 04222 088	EJMM3615T-G	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184JM	1800
027 04222 085	EJMM3613T-G	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184JM	3600
027 04222 095	EJMM3710T-G	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213JM	1800
027 04222 092	EJMM3709T-G	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213JM	3600
027 04222 101	EJMM3714T-G	10HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215JM	1800
027 04222 098	EJMM3711T-G	10HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215JM	3600
027 04222 107	EJMM2333T-G	15HP Motor with TEFC Enclosure (460/230V-3PH-60Hz)	TEFC	254JM	1800
027 04222 104	EJMM2394T-G	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254JM	3600
027 04222 113	EJMM2334T-G	20HP Motor with TEFC Enclosure (460/230V-3PH-60Hz)	TEFC	256JM	1800
027 04222 111	EJMM4106T-G	20HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	256JM	3600

General Purpose, Three Phase, Open Drip Proof, Foot Mounted

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 03647 000	EM3116T	1HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	143T	1800
024 34403 000	EM3116T-8	1HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	143T	1800
027 03683 000	EM3156T	1HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	145T	1200
027 03681 000	EM3216T	1HP Motor with OPSB Enclosure (208/230/460V-3PH-60H)	OPSB	182T	900
027 03690 000	EM3120T	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	143T	3600
027 03648 000	EM3154T	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	145T	1800
024 34421 000	EM3154T-8	1.5HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	145T	1800
027 03687 000	EM3207T	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	182T	1200
027 03685 000	EM3220T	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60H)	OPSB	184T	900
027 03696 000	EM3155T	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	143T	3600
027 03649 000	EM3157T	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	145T	1800
024 34410 000	EM3157T-8	2HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	145T	1800
027 03693 000	EM3215T	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184T	1200
027 03691 000	EM3303T	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60H)	OPSB	213T	900
027 03701 000	EM3158T	3HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	145T	3600
027 03650 000	EM3211T	3HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	182T	1800
027 03697 000	EM3305T	3HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213T	1200
027 03707 000	EM3212T	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	182T	3600
027 03651 000	EM3218T	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184T	1800
027 03703 000	EM3309T	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	215T	1200
027 03702 000	EM2504T	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60H)	OPSB	254T	900
027 03712 000	EM3219T	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184T	3600
027 03652 000	EM3311T	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213T	1800

General Purpose, Three Phase, Open Drip Proof, Foot Mounted

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
024 27058 000	EM3311T-8	7.5HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	213T	1800
027 03708 000	EM2506T	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	254T	1200
027 03718 000	EM3312T	10HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213T	3600
027 03653 000	EM3313T	10HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	215T	1800
024 27060 000	EM3313T-8	10HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	215T	1800
027 03713 000	EM2511T	10HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	256T	1200
027 03724 000	EM3314T	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215T	3600
027 03654 000	EM2513T	15HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	254T	1800
024 27063 000	EM2513T-8	15HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	254T	1800
027 03719 000	EM2524T	15HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	284T	1200
027 03730 000	EM2514T	20HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	254T	3600
027 03655 000	EM2515T	20HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	256T	1800
024 27065 000	EM2515T-8	20HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	256T	1800
027 03726 000	EM2528T	20HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	286T	1200
027 03735 000	EM2516T	25HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	256T	3600
027 03656 000	EM2531T	25HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	284T	1800
027 03732 000	EM2532T	25HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	324T	1200
027 03740 000	EM2534T	30HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	284TS	3600
027 03657 000	EM2535T	30HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	286T	1800
024 27069 000	EM2535T-8	30HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	286T	1800
027 03737 000	EM2536T	30HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	326T	1200
027 03744 000	EM2538T	40HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	286TS	3600
027 03658 000	EM2539T	40HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	324T	1800
027 03849 000	EM2539T-8	40HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	324T	1800
027 03742 000	EM2540T	40HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	364T	1200
027 03748 000	EM2542T	50HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	324TS	3600
027 03659 000	EM2543T	50HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	326T	1800
027 03746 000	EM2544T	50HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	365T	1200
027 03660 000	EM2547T	60HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	364T	1800
024 27075 000	EM2547T-8	60HP Motor with OPSB Enclosure (200V-3PH-60Hz)	OPSB	364T	1800

General Purpose, Three Phase, Totally Enclosed, C-Face, Footless

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04200 000	VEM2394T	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254TC	3600

General Purpose, Three Phase, Totally Enclosed, Foot Mounted

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04095 000	EM3546	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56	1800
027 03495 000	EM3545	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56	3600
027 03662 000	EM3546T	1HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	143T	1800
024 34406 000	EM3546T-8	1HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	143T	1800
027 03763 000	EM3556T	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145T	1200
027 03761 000	EM3617T	1HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	182T	900
027 03496 000	EM3550T	1.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	143T	3600
024 34423 000	EM3554T	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	145T	1800
024 34424 000	EM3554T-8	1.5HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	145T	1800
027 03770 000	EM3618T	1.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	184T	900
027 03664 000	EM3558T	2HP, Motor with TEFC, Enclosure (208/230/460V-3PH-60Hz)	TEFC	145T	1800
024 34413 000	EM3558T-8	2HP Motor with TEFC Enclosure (200/208V-3PH-60Hz)	TEFC	145T	1800
027 03497 000	EM3555T	2HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	145T	3600
027 03776 000	EM3702T	2HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	213T	900
027 03665 000	EM3611T	3HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	182T	1800
024 27081 000	EM3611T-8	3HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	182T	1800
027 03498 000	EM3610T	3HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	182T	3600
027 03785 000	EM3704T	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213T	1200
027 03783 000	EM3705T	3HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	215T	900
027 03666 000	EM3615T	5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	184T	1800
027 04300 030	EM3665T	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184T	1800
027 03499 000	EM3613T	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184T	3600
027 03793 000	EM3708T	5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215T	1200
027 03792 000	EM2280T	5HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	245T	900
027 03500 000	EM3616T	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184T	3600
027 03667 000	EM3710T	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	213T	1800
024 27085 000	EM3770T-8	7.5HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	213T	1800
027 03501 000	EM3709T	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	213T	3600
027 03801 000	EM2276T	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	254T	1200
027 03800 000	EM2401T	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	256T	900
027 03668 000	EM3714T	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215T	1800
024 27087 000	EM3774T-8	10HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	215T	1800
027 03502 000	EM3711T	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215T	3600
027 03809 000	EM2332T	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	256T	1200
027 03808 000	EM2402T	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60H)	TEFC	284T	900
027 03503 000	EM3713T	15HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	215T	3600
027 03669 000	EM2333T	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	254T	1800
024 27089 000	EM2333T-8	15HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	254T	1800
027 03823 000	EM2394T	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	254T	3600
027 03818 000	EM4100T	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	284T	1200
027 03670 000	EM2334T	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	256T	1800
024 27097 000	EM2334T-8	20HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	256T	1800
027 03504 000	EM4106T	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	256T	3600

General Purpose, Three Phase, Totally Enclosed, Foot Mounted

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 03826 000	EM4102T	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	286T	1200
027 03825 000	EM4112T	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	324T	900
027 03514 000	EM4103T	25HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	284T	1800
024 27099 000	EM4103T-8	25HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	284T	1800
027 03505 000	EM4107T	25HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	284TS	3600
027 03833 000	EM4111T	25HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	324T	1200
027 03515 000	EM4104T	30HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	286T	1800
024 34433 000	EM4104T-8	30HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	286T	1800
027 03506 000	EM4108T	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	286TS	3600
027 03844 000	EM4108T-8	30HP Motor with TEFC Enclosure (208V-3PH-60Hz)	TEFC	286TS	3600
027 03840 000	EM4117T	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	326T	1200
027 01368 000	EM4110T	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	324T	1800
024 34437 000	EM4110T-8	40HP Motor with TEFC Enclosure (200V-3PH-60Hz)	TEFC	324T	1800
027 03507 000	EM4109T	40HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	324TS	3600
027 03847 000	EM4308T	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	364T	1200
027 03517 000	EM4115T	50HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	326T	1800
027 03508 000	EM4114T	50HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	326TS	3600
027 03852 000	EM4312T	50HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	365T	1200
027 03518 000	EM4314T	60HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	364T	1800
027 03509 000	EM4310T	60HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	364TS	3600
027 03858 000	EM4403T	60HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	404T	1200

Jet Pump, Three Phase, TEFC, Footless

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 04222 057	EJM3546	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	1800
027 04222 053	EJM3545	1HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	3600
027 04222 062	EJM3554	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	1800
027 04222 058	EJM3550	1.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	3600
027 04222 073	EJM3558	2HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	1800
027 04222 066	EJM3555	2HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	3600
027 04222 074	EJM3559	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	56J	3600



Super-E®, Three Phase, ODP, Foot Mounted, with Internal Aegis Bearing Protection Ring

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 03113 000	EM3116T-G	1HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	143T	1800
027 03682 000	EM3156T-G	1HP Motor with OPSB Enclosure (208/230V-3PH-60Hz)	OPSB	145T	1200
027 03689 000	EM3120T-G	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	143T	3600
027 03114 000	EM3154T-G	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	145T	1800
027 03686 000	EM3207T-G	1.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	182T	1200
027 03695 000	EM3155T-G	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	143T	3600
027 03546 000	EM3157T-G	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	145T	1800
027 03692 000	EM3215T-G	2HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184T	1200
027 03700 000	EM3158T-G	3HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	145T	3600
027 03116 000	EM3211T-G	3HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	182T	1800
027 03698 000	EM3305T-G	3HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213T	1200
027 03706 000	EM3212T-G	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	182T	3600
027 03117 000	EM3218T-G	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184T	1800
027 03704 000	EM3309T-G	5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	215T	1200
027 03711 000	EM3219T-G	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	184T	3600
027 03120 000	EM3311T-G	7.5HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	213T	1800
027 03709 000	EM2506T-G	7.5HP Motor with OPSB Enclosure (208V-3PH-60Hz)	OPSB	254T	1200
027 03716 000	EM3313T-8G	10HP Motor with OPSB Enclosure (132V-3PH-60Hz)	OPSB	215T	1800
027 03121 000	EM3313T-G	10HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215T	1800
027 03714 000	EM2511T-G	10HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	256T	1200
027 03723 000	EM3314T-G	15HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	215T	3600
027 03123 000	EM2513T-G	15HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	254T	1800
027 03720 000	EM2524T-G	15HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	284T	1200
027 03729 000	EM2514T-G	20HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	254T	3600
027 03126 000	EM2515T-G	20HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	256T	1800
027 03725 000	EM2528T-G	20HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	286T	1200
027 03734 000	EM2516T-G	25HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	256T	3600
027 03127 000	EM2531T-G	25HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	284T	1800
027 03731 000	EM2532T-G	25HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	324T	1200
027 03739 000	EM2534T-G	30HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	284TS	3600
027 03129 000	EM2535T-G	30HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	286T	1800
027 03736 000	EM2536T-G	30HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	326T	1200
027 03745 000	EM2538T-G	40HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	286TS	3600
027 03131 000	EM2539T-G	40HP Motor with OPSB Enclosure (230/460V-3PH-60Hz)	OPSB	324T	1800
027 03741 000	EM2540T-G	40HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	364T	1200
027 03749 000	EM2542T-G	50HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	324TS	3600
027 03134 000	EM2543T-G	50HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	326T	1800
027 03135 000	EM2547T-G	60HP Motor with OPSB Enclosure (208/230/460V-3PH-60Hz)	OPSB	364T	1800

Super-E®, Three Phase, TEFC, Foot Mounted, with Internal Aegis Bearing Protection Ring

Item	Vendor PN	Description	Enclosure Type	Frame Size	RPM
027 03769 000	EM3545-G	1HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	56	3600
027 03766 000	EM3546T-G	1HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	143T	1800
027 03762 000	EM3556T-G	1HP Motor with TEFC Enclosure (208/230V-3PH-60Hz)	TEFC	145T	1200
027 03774 000	EM3550T-G	1.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	143T	3600
027 03115 000	EM3554T-G	1.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	145T	1800
027 03771 000	EM3607T-G	1.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	182T	1200
027 03778 000	EM3558T-G	2HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	145T	1800
027 03781 000	EM3555T-G	2HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	145T	3600
027 03777 000	EM3614T-G	2HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	184T	1200
027 03790 000	EM3559T-G	3HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	145T	3600
027 03784 000	EM3704T-G	3HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	213T	1200
027 03118 000	EM3615T-G	5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	184T	1800
027 03798 000	EM3613T-G	5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	184T	3600
027 03794 000	EM3708T-G	5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215T	1200
027 03119 000	EM3710T-G	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	213T	1800
027 03807 000	EM3709T-G	7.5HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	213T	3600
027 03802 000	EM2276T-G	7.5HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	254T	1200
027 03122 000	EM3714T-G	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215T	1800
027 03815 000	EM3711T-G	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	215T	3600
027 03810 000	EM2332T-G	10HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	256T	1200
027 03787 000	EM3611T-G	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	182T	1800
027 03124 000	EM2333T-G	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	254T	1800
027 03824 000	EM2394T-G	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	254T	3600
027 03817 000	EM4100T-G	15HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	284T	1200
027 03125 000	EM2334T-G	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	256T	1800
027 03832 000	EM4106T-G	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	256T	3600
027 03827 000	EM4102T-G	20HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	286T	1200
027 03128 000	EM4103T-G	25HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	284T	1800
027 03838 000	EM4107T-G	25HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	284TS	3600
027 03834 000	EM4111T-G	25HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	324T	1200
027 03130 000	EM4104T-G	30HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	286T	1800
027 03843 000	EM4108T-G	30HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	286TS	3600
027 03839 000	EM4117T-G	30HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	326T	1200
027 03132 000	EM4110T-G	40HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	324T	1800
027 03851 000	EM4109T-G	40HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	324TS	3600
027 03846 000	EM4308T-G	40HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	364T	1200
027 03133 000	EM4115T-G	50HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	326T	1800
027 03856 000	EM4114T-G	50HP Motor with TEFC Enclosure (208/230/460V-3PH-60Hz)	TEFC	326TS	3600
027 03853 000	EM4312T-G	50HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	365T	1200
027 03136 000	EM4314T-G	60HP Motor with TEFC Enclosure (230/460V-3PH-60Hz)	TEFC	364T	1800