



**YORK**

# LX series

AIR CONDITIONERS & HEAT PUMPS




## LX Series AC and HP (Louvered Microchannel Unit)

### For you, the dealer

- Microchannel coil technology for AC (makes it ideal for coastal applications—lasts seven times longer); HP models feature copper tube/aluminum fin
- R22 and R410A
- 13 SEER R22 models do not require a TXV
- One of the smallest footprints in the industry (ideal for townhomes, row homes and zero lot lines)
- Reduced weight (up to 30%)
- 50% less refrigerant required (reduces overall system cost and makes product more "green")
- Easy to clean, service and repair



### For your customer

- Fully louvered coil protection with secondary mesh
- Powder-painted steel
- 13 and 14.5 SEER (1-stage); higher with variable-speed indoor units
- Compressor blanket
- Swept wing fan blade (14.5 SEER only)
- Quieter, richer sound versus standard-tier microchannel products
- 14.5 SEER models are ENERGY STAR<sup>®</sup> qualified 

## LX Series AC and HP Models

LX SERIES AIR CONDITIONERS				DIMENSIONS			LIMITED WARRANTY	
Model	Tonnage	Nominal Efficiency	Refrigerant	Height	Width	Length	Parts	Compressor
YCJD18S41S1	1.5 Ton	13 SEER	R410A	28"	23.6"	23.6"	5-Year	10-Year
YCJD24S41S1	2.0 Ton	13 SEER	R410A	28"	23.6"	23.6"	5-Year	10-Year
YCJD30S41S1	2.5 Ton	13 SEER	R410A	28"	23.6"	23.6"	5-Year	10-Year
YCJD36S41S1	3.0 Ton	13 SEER	R410A	28"	29"	29"	5-Year	10-Year
YCJD42S41S1	3.5 Ton	13 SEER	R410A	30"	29"	29"	5-Year	10-Year
YCJD48S41S1	4.0 Ton	13 SEER	R410A	30"	29"	29"	5-Year	10-Year
YCJD60S41S1	5.0 Ton	13 SEER	R410A	32"	33.6"	33.6"	5-Year	10-Year
YCJD18S21S1	1.5 Ton	13 SEER	R22	28"	23.6"	23.6"	5-Year	10-Year
YCJD24S21S1	2.0 Ton	13 SEER	R22	28"	23.6"	23.6"	5-Year	10-Year
YCJD30S21S1	2.5 Ton	13 SEER	R22	32"	23.6"	23.6"	5-Year	10-Year
YCJD36S21S1	3.0 Ton	13 SEER	R22	34"	23.6"	23.6"	5-Year	10-Year
YCJD42S21S1	3.5 Ton	13 SEER	R22	34"	29"	29"	5-Year	10-Year
YCJD48S21S1	4.0 Ton	13 SEER	R22	34"	29"	29"	5-Year	10-Year
YCJD60S21S1	5.0 Ton	13 SEER	R22	40"	29"	29"	5-Year	10-Year
YCJF24S41S1	2.0 Ton	14.5 SEER	R410A	*32"	23.6"	23.6"	5-Year	10-Year
YCJF30S41S1	2.5 Ton	14.5 SEER	R410A	32"	29"	29"	5-Year	10-Year
YCJF36S41S1	3.0 Ton	14.5 SEER	R410A	32"	29"	29"	5-Year	10-Year
YCJF42S41S1	3.5 Ton	14.5 SEER	R410A	30"	33.6"	33.6"	5-Year	10-Year
YCJF48S41S1	4.0 Ton	14.5 SEER	R410A	32"	33.6"	33.6"	5-Year	10-Year
YCJF60S41S1	5.0 Ton	14.5 SEER	R410A	36"	33.6"	33.6"	5-Year	10-Year

\* Preliminary data. Subject to change.

LX SERIES HEAT PUMPS				DIMENSIONS			LIMITED WARRANTY	
Model	Tonnage	Nominal Efficiency	Refrigerant	Height	Width	Length	Parts	Compressor
YHJD18S41S1	1.5 Ton	13 SEER	R410A	24"	33.6"	33.6"	5-Year	10-Year
YHJD24S41S1	2.0 Ton	13 SEER	R410A	28"	33.6"	33.6"	5-Year	10-Year
YHJD30S41S1	2.5 Ton	13 SEER	R410A	32"	33.6"	33.6"	5-Year	10-Year
YHJD36S41S1	3.0 Ton	13 SEER	R410A	36"	33.6"	33.6"	5-Year	10-Year
YHJD42S41S1	3.5 Ton	13 SEER	R410A	36"	33.6"	33.6"	5-Year	10-Year
YHJD48S41S1	4.0 Ton	13 SEER	R410A	36"	33.6"	33.6"	5-Year	10-Year
YHJD60S41S1	5.0 Ton	13 SEER	R410A	36"	33.6"	33.6"	5-Year	10-Year



Unitary Products Group, Inc. 5005 York Drive, Norman, OK 73069 www.yorkupg.com  
 Subject to change without notice. Copyright © by York International Corporation 2008.  
 362103-YSS-D-0708 Supersedes: 362103-YSS-C-0508. All rights reserved.