CATALOG

 \Box

FW and FL Fan-Coil Units Floor-Mounted, Vertical





TABLE OF CONTENTS

Features and Benefits
Construction Features
Standard and Optional Features9
Coil Data
Physical Data
Electric Heat
Fan Performance
Motor and Fan Data
Sound Data
Dimensional Data
Piping Packages
Guide Specifications





- Johnson Controls offers Web-Select[®], the industry's first web-based rating and selection program for complete unit, coil and sound selection. See your representative for more information.
- Some drawings are not shown in this catalog.
- All data herein is subject to change without notice.
- Drawings not for installation purposes.
- ETL Report Number 3096645CRT-002.

FEATURES AND BENEFITS

DESIGN FLEXIBILITY

The Johnson Controls vertical floor mounted fan coil units are designed to maximize flexibility of selection and installation.

The units are also designed to exceed the stringent quality standards of the institutional market, while remaining cost competitive in the light commercial segment of the market.

Johnson Controls vertical fan coil units set the new standards for quality, flexibility, and competitive pricing.

DESIGN FLEXIBILITY

The extensive variety of standard options available on vertical floor fan coil units are where you find the versatility to fit any HVAC system designer's needs. Models FWX and FWI allow for additional height and width dimensions to meet architectural demand.

Options include: single wall stainless steel drain pan; MERV 7, MERV 8 and MERV 13 filters; and electric heat with single point power connection. All electric heat units are listed with ETL as an assembly and carry the cETL label.

All units comply with the latest edition of AHRI Standard 440 for testing and rating fan coil units, are certified, and display the AHRI symbol.

High efficiency motors, fan relays, disconnects and fusing mean easier coordination between mechanical and electrical trades.

Coil options allow for three or four row chilled water or DX cooling coils, and one or two row hot water or steam heating coils.

Silent solid state relays are available for fan and electric heat control in sound sensitive environments.

CONVENIENT INSTALLATION

All vertical floor fan coils are shipped completely assembled, reducing field installation time and labor. All units are thoroughly inspected and tested prior to shipment, eliminating potential problems at startup. Motor wiring is brought to a junction box on the inside of the unit end pocket, reducing electrical hook-up time.

Factory furnished valve packages assure proper fit, operation and performance.

For fast track jobs, the vertical floor fan coil is available on Quick Ship with 5, 10 or 15 day lead times.

OPTIMUM BUILDING PERFORMANCE

Concealed vertical floor fan coil chassis are built from galvanized steel. This metal surpasses the ASTM 125 hour salt spray test for corrosion and rust. Exposed cabinet models are powder coated galvannealed steel.

All units, with or without electric heat, are cETL listed and labeled. All wiring is in compliance with NEC, assuring safety and quality for the owner.


Floor mounted cabinet models feature finned tubular heating elements in the reheat position, protecting room occupants from electrical shock.

Vertical floor fan coil units have a removable fan/drain pan assembly. The entire fan assembly can be easily removed from the unit and serviced on a workbench.

Filters are easily replaceable from the return air toe space without the need for tools or removal of the front panel (FW only).

MODEL FWX & FLX

(Photo as shown for FWX). FW and FL Series fan coils have many standard and optional features which are unique to the industry. See page 6 for a complete listing.



MODELS FWX/FWI/FWC



END POCKETS

The 8" end pockets allow for accessibility and service of optional factory piping packages and controls. End panels are removable to allow for even greater access.



FAN DECK

The fan/drain pan assembly is easily removable for service access to motors and blowers at, or away from, the unit.

DRAIN PAN

The sloped insulated primary drain pan is available in stainless steel construction. Standard drain pan is externally insulated, single wall galvanized steel. The FW Series fan/drain pan assembly is easily removable for cleaning.



COILS

All fan coils are available in 2 or 4 pipe configurations. The heating coil is standard in the reheat position. Heating and cooling coils are available with the same or opposite end connections. Access for cleaning on the entering air side is available when the drain pan is removed. Coils are removable for service.



FILTER

The filter is easily replaceable through the return air toe space without requiring removal of the front panel.

POWDER COATED PAINTED SURFACE

Exposed cabinet Models FWX and FWI, as well as

supply and return air grilles and the FWC wall recessing panel, feature a powder coat finish that resists scuffing, scratching, fading, and fingerprints.





CONTROL ENCLOSURE

The FW control enclosure provides adequate space for the unit controller and fan coil relay. The fan coil relay is designed to limit diagnostic problems, while allowing for multi-voltage fan power input. The board is designed for factory installed, color coded, plug and play connections designed to ensure accurate wiring.

MODELS FWX/FWI/FWC



PIPING PACKAGES

Factory installed piping packages come equipped with components specific to the project. Actuators ship with color coded plug and play connections for quick, accurate installations.




FAN DECK REMOVAL

FW units allow for a single technician to service the fan/motor by keeping the fan deck to less than 44". Motors are supplied with quick connectors to allow electrical service without the need for tools.



LID REMOVAL Top panel is removable from fan coil without the need to disconnect piping or electrical wires.



END POCKETS

The 8" end pockets allow for accessibility and service of optional factory piping packages and controls. End panels are removable to allow for even greater access.



FAN DECK

The fan/drain pan assembly is easily removable for service access to motors and blowers at, or away from, the unit.

DRAIN PAN

The sloped insulated primary drain pan is available in stainless steel construction. The standard drain pan is externally insulated, single wall galvanized steel. A non-metallic auxiliary drip pan is provided as standard. The FL Series fan/drain pan assembly is easily removable for cleaning.



COILS

MODELS FLX/FLC

All units are available in 2 or 4 pipe configurations. The heating coil is standard in the reheat position. Heating and cooling coils are available with same end connections. Access for cleaning on the entering air side is available when the drain pan is removed. Coils are removable for service.



FILTER

The filter is easily replaceable through the return air toe space without requiring removal of the front panel.

POWDER COATED PAINTED SURFACE

Exposed cabinet Model FLX, as well as supply and return air grilles and the FLC wall recessing panel, feature a powder coat finish that resists scuffing, scratching, fading, and fingerprints.



ELECTRICAL ENCLOSURE

The front access electrical enclosure provides access to all electric heat and control components. Terminal strips are furnished for simple power and control wiring connections. Multiple knockouts allow wiring entries from either the top or bottom of the compartment.



CONCEALED MODEL FLC

For built-in applications, Model FLC features a 1" top supply with duct collar.

ELECTRIC HEAT

MODELS FLX/FLC

A variety of kW and voltage configurations are available. Options include door interlock disconnects, low voltage controls, and silent solid state relays. All control and electric heat configurations include single point power connection and are cETL listed as an assembly.



STANDARD AND OPTIONAL FEATURES

STANDARD FEATURES

Construction

All Units

- · AHRI 440 certified and labeled
- Galvanized steel construction
- Insulation, FW: elastomeric closed cell foam
- Insulation, FL: 1/2" thick fiberglass insulation
- · Integral filter rack with 1" throwaway filter

Concealed Units

· Top supply with duct collar

Exposed Units

- Top stamped louver supply grille
- · Durable powder coat paint
- End pockets with removable panels
- 20 gauge exterior panel construction
- Flat top
- Sloped top (FW only)

Coils

- · Cooling 3 or 4 row chilled water or DX, heat pump compatible
- Heating 1 or 2 row hot water or steam reheat position
- 1/2" O.D. seamless copper tubes
- 0.016" tube wall thickness
- · High efficiency aluminum fin surface for optimizing heat transfer, pressure drop and carryover
- Left or right hand, same or [opposite FW only] end connections
- Removable for service
- · Manual air vents

Drain Pans

- Single wall, galvanized steel, externally insulated fire retardant and antimicrobial
- Positively sloped to drain connection
- 3/4" M.P.T. auxiliary drain pan connection
- Double wall plastic auxiliary drip pan

Fan Assemblies

- · Forward curved, DWDI centrifugal type
- 115 volt, single phase, three speed PSC motors
- Quick disconnect motor connections
- · Removable for service

Electrical

- · cETL listed for safety compliance
- · Electrical junction box for field wiring terminations
- · Terminal block for field connections

Electric Heat

- · Finned tubular element on all floor mounted units protects against electrical shock
- ETL listed as an assembly for safety compliance
- · Integral electric heat assembly with removable elements for easy service
- Automatic reset primary and back-up secondary thermal limits
- Single point power connection

OPTIONAL FEATURES

Construction

- All Units
- Foil faced fiberglass insulation (FL)
- · Elastomeric closed cell foam insulation (FL)
- · Manual and motorized outside air dampers
- Spare 1" throwaway filters
- 1" pleated filters (MERV 7)

Johnson Controls

- Wall boxes (FW only)
- Leveling legs
- Concealed Units · Wall recessing panels (FW only)
- Exposed Units
- · Linear bar discharge grille, powder coated
- 16 gauge front panel (FW only)
- Return air louver grille
- 2" 8" falsebacks (FW only)
- Extended end pockets (FW only)
- Tamper proof fasteners

Coils

- · Automatic air vents
- · Stainless steel coil casings
- 0.025" tube wall (standard on steam)

Drain Pans

- · Stainless steel construction with external insulation
- · Double wall plastic auxiliary drain pan extended length (FW only)
- Stainless steel auxiliary drain pan extended length (FW only)

Fan Assemblies

• 208-230 & 277 volt, 60 Hz and 220 volt, 50 Hz motors

Electrical

- · Electronically commutated motors
- SCR fan speed controller (high speed only)
- · Fan relay packages
- Silent solid state fan relays (FW only)
- Toggle disconnect switch
- Condensate overflow switch (auxiliary drain pan)
- Main fusing
- Unit and remote mounted three speed fan switches
- Unit and remote mounted 3-speed fan switches (unit mounted three speed switch is located under access door on exposed and slope top vertical floor mount unit's. Unit mounted three-speed switch is located within control enclosure on vertical low profile units)

Electric Heat

- · Door interlocking disconnect switches
- Main fusing
- Silent relay/contactors (FW only)

Piping Packages

Unit and remote mounted, with integral three speed fan

9

- Factory assembled shipped loose for field installation
 1/2" and 3/4", 2-way and 3-way normally closed, two position electric motorized valves
- İsolation ball valves with memory stop
- 4 pipe with 3-way valve (FW only)
- · Fixed and adjustable flow control devices

· Analog, digital display, or programmable

- Unions and P/T ports
- Modulating control valves

Thermostats

switch

 High pressure close-off actuators (1/2" = 50 PSIG; 3/4" = 25 PSIG)

2 and 4-pipe control sequences

· Automatic and manual changeover

COIL DATA: FW SERIES

COILS

Johnson Controls offers hot water, chilled water, direct expansion (DX - FW only), and standard single tube steam coils for specific application with all Vertical Floor fan coil units. Strict on-site inspection before, during, and after installation guarantees the highest quality and performance available.

STANDARD FEATURES

- · Cooling 3 or 4 row chilled water or [DX FW only]
- Heating 1 or 2 row hot water or steam
- Total rows of cooling and heating coils: FW: 4 maximum, FL: 5 maximum
- 1/2" O.D. seamless copper tubes
- 0.016" tube wall thickness
- High efficiency aluminum fin surface for optimizing heat transfer, pressure drop and carryover
- Left or right hand, same or [opposite side FW only] connections
- Manual air vents

OPTIONAL FEATURES

- Automatic air vents
- Stainless steel coil casings
- 0.025" tube wall thickness (standard on steam coils)
- DX coils (FW only) are heat pump compatible

Johnson Controls offers Web-Select[®] fan coil rating and selection program for complete unit, coil and sound selection. See your representative for more information.

FW NOMINAL COIL CONNECTION SIZES

	COIL TYPE											
UNIT	нот и	HOT WATER CHILLED WATER STEAM REFRIGERANT (DX)										
SIZE	1 ROW	2 ROW	3 ROW	4 ROW	1 ROW	2 ROW	2 R	ow	3 R	ow	4 ROW	
	INOW	2 10 10	3 10 10	4 10 10	INOW	2 1000	Liquid	Suction	Liquid	Suction	Liquid	Suction
02 - 12	5/8 [16]	5/8 [16]	5/8 [22]	5/8 [22]	5/8 [16]	5/8 [16]	3/8 [10]	5/8 [16]	3/8 [10]	5/8 [16]	3/8 [10]	5/8 [16]

NOTES:

1. Connection sizes are for standard circuit coils. Consult factory for special applications.

2. See submittal drawings for connection locations.

3. All dimensional data is outside diameter (O.D.), measured in inches [millimeters].

FW FACE AREA, FREE AREA AND FILTER SIZES

UNIT SIZE	COIL FACE AREA	DISCHARGE GRILLE FREE AREA	FILTER FACE AREA	NOMINAL FILTER SIZES
02	0.97 [.090]	0.47 [.044]	1.40 [.130]	9.25 X 21.75 X 1 [235 X 552 X 25.4]
03	1.25 [.116]	0.56 [.052]	1.65 [.154]	9.25 X 25.75 X 1 [235 X 654 X 25.4]
04	1.67 [.155]	0.66 [.061]	2.04 [.189]	9.25 X 31.75 X 1 [235 X 806 X 25.4]
06	2.36 [.219]	0.94 [.087]	2.68 [.249]	9.25 X 41.75 X 1 [235 X 1060 X 25.4]
08	2.50 [.023]	0.94 [.087]	2.79 [.260]	(2) 9.25 X 21.75 X 1 [235 X 552 X 25.4]
10	2 47 [222]	1 21 [122]	2 60 [242]	(1) 9.25 X 25.75 X 1 [235 X 654 X 25.4]
10	3.47 [.322]	1.31 [.122]	3.69 [.343]	(1) 9.25 X 31.75 X 1 [235 X 806 X 25.4]
12	4.03 [.374]	1.50 [.139]	4.19 [.389]	(3) 9.25 X 21.75 X 1 [235 X 552 X 25.4]

NOTES:

1. Face and free areas are in square feet [square meters].

2. Filter sizes are in inches [millimeters].

FW HEATING CAPACITY

UNIT TYPE	UNIT	NOM.	1	ROW		2	ROW	
ONIT TIPE	SIZE	CFM	QS (MBH)	GPM	WPD	QS (MBH)	GPM	WPD
FW	02	230	7856	0.4	0.2	14273	0.7	1.0
FW	03	300	10980	0.6	0.4	19151	1.0	1.9
FW	04	430	15945	0.8	0.8	27475	1.4	4.2
FW	06	540	21791	1.1	1.7	36747	1.9	8.8
FW	08	600	23847	1.2	2.1	40072	2.1	10.7
FW	10	830	34277	1.8	5.1	54722	2.8	3.4
FW	12	920	38814	2.0	7.0	62206	3.2	4.7

NOTE: Based on 70°F DB EAT, 180°F EWT, 40°F temperature drop, high fan speed.

COIL DATA: FL SERIES

FL	. NOMII	VAL CO	IL CON	NECTIO	ON SIZI	ES
			COIL CONN	ECTION SIZE		
UNIT		HOT WATER		CI	HILLED WATE	ER
SIZE	1 ROW	2 ROW	3 ROW	2 ROW	3 ROW	4 ROW

5/8 [16]

5/8 [16]

5/8 [16]

5/8 [16]

5/8 [16]

5/8 [16]

5/8 [16]

7/8 [19]

NOTES:

02 & 03

04 & 06

1. Connection sizes are for standard circuit coils. Consult factory for special applications.

2. See submittal drawings for connection locations.

5/8 [16]

5/8 [16]

5/8 [16]

5/8 [16]

3. All dimensional data is outside diameter (O.D.), measured in inches [millimeters].

FL FACE AREA AND FILTER SIZES

UNIT SIZE	COIL FACE AREA	DISCHARGE GRILLE DIMENSIONS	FILTER FACE AREA	NOMINAL FILTER SIZES
02	1.18 [0.11]	17 x 5.25 [432 x 133]	1.12 [0.10]	21.5 x 7.5 [546 x 191]
03	1.53 [0.14]	22 x 5.25 [559 x 133]	1.38 [0.13]	26.5 x 7.5 [673 x 191]
04	2.08 [0.19]	30 x 5.25 [762 x 133]	1.80 [0.17]	34.5 x 7.5 [876 x 191]
06	3.06 [0.28]	44 x 5.25 [1118 x 133]	2.53 [0.23]	48.5 x 7.5 [1232 x 191]

NOTES:

1. Face and free areas are in square feet [square meters].

2. Filter sizes are in inches [millimeters].

FL HEATING CAPACITY

UN	IT	UNIT	NOM.	1 ROW			2 ROW			3 ROW		
TY	PE	SIZE	CFM	QS (MBH)	GPM	WPD	QS (MBH)	GPM	WPD	QS (MBH)	GPM	WPD
		02	200	9.2	0.6	0.6	15.4	1.1	2.6	19.0	1.3	5.7
FL	С	03	300	13.4	0.9	1.2	22.4	1.5	5.6	27.2	1.9	2.0
FL	x	04	400	18.5	1.3	2.4	30.4	2.1	11.1	37.0	2.5	3.9
		06	600	28.2	1.9	6.0	44.8	3.1	4.7	56.0	3.8	9.8

Note: Based on 70°F DB EAT, 180°F EWT, 30°F temperature drop, high fan speed.

PHYSICAL DATA: FW SERIES

FW AHRI STANDARD RATINGS

	cc	DIL	AIRFLOW	COOLING	CAPACITY	WA	TER	POWER
MODEL / SIZE	Rows	FPI	CFM (dry flow)	QT (BTUH)	QS (BTUH)	Flow Rate (GPM)	WPD ft-wg	INPUT (WATTS)
02	3	10	230	5600	3700	1.5	6.5	45
03	3	10	320	6900	5000	1.8	9	60
04	3	10	450	12300	8700	3	3.91	70
06	3	10	570	16900	11700	4.4	8.11	80
08	3	10	630	18600	12900	4.8	10.07	114
10	3	10	835	24700	17100	6.3	7.01	132
12	3	10	980	28000	19100	7.4	10.56	142

FW UNIT WEIGHT DATA

	COMPONENT FWC BASE UNIT FWX BASE UNIT FWI BASE UNIT 1 ROW - DRY 1 ROW - WET 2 ROW - DRY 2 ROW - DRY				UNIT SIZE			
	JIVIPONENT	02	03	04	06	08	10	12
FWC BASE UNIT		36 [16]	45 [20]	55 [25]	62 [28]	66 [30]	92 [42]	105 [48]
FW	FWX BASE UNIT		74 [34]	87 [39]	96 [44]	102 [46]	131 [59]	149 [68]
FWI BASE UNIT		68 [31]	76 [34]	89 [40]	99 [45]	102 [46]	135 [61]	153 [69]
	1 ROW - DRY	11 [5]	12 [5]	14 [6]	18 [8]	19 [9]	23 [10]	26 [12]
	1 ROW - WET	14 [6]	15 [7]	20 [9]	24 [11]	25 [11]	32 [15]	37 [17]
	2 ROW - DRY	14 [6]	15 [7]	19 [9]	22 [10]	24 [11]	30 [14]	33 [15]
TOTAL COIL	2 ROW - WET	19 [9]	20 [9]	25 [11]	31 [14]	32 [15]	41 [19]	47 [21]
ROWS	3 ROW - DRY	18 [8]	20 [9]	23 [10]	29 [13]	30 [14]	37 [17]	43 [20]
	3 ROW - WET	23 [10]	25 [11]	32 [15]	39 [18]	41 [19]	52 [24]	61 [28]
	4 ROW - DRY	22 [10]	25 [11]	30 [14]	36 [16]	39 [18]	47 [21]	54 [24]
	4 ROW - WET	30 [14]	32 [15]	41 [19]	50 [23]	52 [24]	65 [29]	77 [35]

NOTE: Unit weight data is in pounds [kilograms].

PHYSICAL DATA: FL SERIES

	COI	L	AIRFLOW	COOLING	COOLING CAPACITY		WATER		
MODEL / SIZE	ROWS	FPI	CFM	QT	QS	Flow Rate	WPD	INPUT	
	KO WS	FFI	(DRY FLOW)	(MBH)	(MBH)	(GPM)	FT. WG.	(WATTS)	
FLC/FLX 02	3		200	6500	4300	1.6	11.7	75	
FLC/FLX 03	3	10	300	9500	6500	2.0	3.4	75	
FLC/FLX 04	3	10	400	14000	9500	2.9	7.4	75	
FLC/FLX 06	3		600	20000	15000	5.2	9.9	140	

FL AHRI STANDARD RATINGS

NOTE: Based on 80°F DB and 67°F WB EAT, 45°F EWT, 10°F temperature rise, high fan speed. Motor type is PSC and motor voltage is 115/1/60. Airflow under dry coil conditions. Model FLX tested at 0.0" external static pressure. Model FLC tested at 0.05" external static pressure.

	COMPONENT		UNITS	SIZE	
	COMPONENT	02	03	04	06
FLC B	ASE UNIT, STD HEIGHT	51 [23]	58 [26]	65 [29]	77 [35]
FLC B	ASE UNIT, EXT HEIGHT	65 [29]	69 [31]	74 [34]	84 [38]
FLX B	ASE UNIT, STD HEIGHT	90 [41]	97 [44]	104 [47]	116 [53]
FLX B	ASE UNIT, EXT HEIGHT	104 [47]	108 [49]	113 [51]	123 [56]
	1 ROW - DRY	11 [5]	13 [6]	15 [7]	17 [8]
	1 ROW - WET	14 [6]	17 [8]	20 [9]	23 [10]
	2 ROW - DRY	14 [6]	17 [8]	20 [9]	22 [10]
	2 ROW - WET	20 [9]	25 [11]	30 [13]	34 [15]
TOTAL COIL	3 ROW - DRY	19 [8]	22 [10]	25 [11]	29 [13]
ROWS	3 ROW - WET	28 [13]	34 [15]	40 [18]	47 [21]
	4 ROW - DRY	24 [11]	29 [13]	33 [15]	37 [17]
	4 ROW - WET	36 [16]	45 [20]	53 [24]	61 [28]
	5 ROW - DRY	31 [14]	37 [17]	43 [19]	49 [22]
	5 ROW - WET	46 [21]	57 [26]	68 [31]	79 [36]

FL UNIT WEIGHT DATA

NOTE: Unit weight data is in pounds [kilograms].

ELECTRIC HEAT

Johnson Controls offers electric heating coils for specific application with all Vertical Floor Series Fan Coil units. This allows the flexibility to provide an unrivaled amount of electric heat options in one complete package.

NTERTE

STANDARD FEATURES

- · ETL listed as an assembly for safety compliance
- Single point power connection
- Mounted in reheat position (FW)[Preheat fo FL]
- Automatic reset primary and back-up secondary thermal limits
- Internal wiring rated at 105°C
- Integral electric heat assembly with removable element for easy service
- Stainless steel terminals and hardware
- Finned tubular heater virtually eliminates the risk of shock from accidental contact.

OPTIONAL FEATURES

- · Silent solid state relays (FW only) on heaters up to 18 amps
- Door interlocking disconnect switch
- Main fusing (Branch fusing for EH > 48 amps)



 $10 \text{ AMPs} = \frac{\text{kW x 1000}}{\text{Volts}}$

* 1kW = 3413 BTU/H

** Capacity at sea level Altitude Considerations:

Reduce by 0.034 for each 1000 ft. of altitude above sea level.

<u>CFM x <u>A</u>T x 1.085**</u>

3413

Example: 5000 ft./1000 ft. = 5 5 x 0.034 = 0.17 1.085 - 0.17 = 0.915

ELECTRICAL CALCULATIONS INFORMATION

- 1. Contact your local Johnson Controls sales office.
- 2. Non-Fused Door Interlock Disconnect Switch shall be sized according to MCA.
- 3. Fused Door Interlock Disconnect Switch and Main Fusing shall be sized according to MOP.

	МВН	3.4	5.1	6.8	10.2	13.7	17.1	20.5				
UNIT SIZE	ĸw	1.0	1.5	2.0	3.0	4.0	5.0	6.0				
SIZE	VOLTS	AMPS										
	115	8.3										
02	208	4.8										
02	240	4.2										
	277	3.6										
	115	8.3	12.5									
03	208	4.8	7.2									
03	240	4.2	6.3									
	277	3.6	5.4									
	115	8.3	12.5	16.7								
04	208	4.8	7.2	9.6								
	240	4.2	6.3	8.3								
	277	3.6	5.4	7.2								
	115	8.3	12.5	16.7	25.0							
06	208	4.8	7.2	9.6	14.4							
00	240	4.2	6.3	8.3	12.5							
	277	3.6	5.4	7.2	10.8							
	115	8.3	12.5	16.7	25.0							
08	208	4.8	7.2	9.6	14.4	19.2						
08	240	4.2	6.3	8.3	12.5	16.7						
	277	3.6	5.4	7.2	10.8	14.4						
	115	8.3	12.5	16.7	25.0							
10	208	4.8	7.2	9.6	14.4	19.2	24.0					
10	240	4.2	6.3	8.3	12.5	16.7	20.8					
12	277	3.6	5.4	7.2	10.8	14.4	18.1					
	115	8.3	12.5	16.7	25.0							
	208	4.8	7.2	9.6	14.4	19.2	24.0	28.9				
12	240	4.2	6.3	8.3	12.5	16.7	20.8	25.0				
	277	3.6	5.4	7.2	10.8	14.4	18.1	21.7				

FW ELECTRIC HEAT SELECTION CHART (AMPS)

NOTES:

- Shaded areas of the electric heat selection chart indicate kW and voltage options not available.
- 2. Available voltages are single phase, 60 hertz.
- 3. Size heater for Leaving Air Temperature (LAT) less than 104°F.
- 4. Silent, solid state heater relay is available for heater currents less than 18 amps.
- 5. Ask your representative about continuously modulating electric heat using SSR and special control options.

FL ELECTRIC HEAT SELECTION CHART (AMPS)

	MBH	3.4	5.1	6.8	10.2	NOTES:
UNIT SIZE	KW	1.0	1.5	2.0	3.0	1. See notes 1 through 3 abov
SIZE	VOLTS		AN	1PS	-	
	115	8.7				
02	208	4.8				
02	230	4.4				
	277	3.6				
	115	8.7	13.1			
03	208	4.8	7.2			
05	230	4.4	6.5			I
	277	3.6	5.4			
	115	8.7	13.1	17.4	26.1	
04	208	4.8	7.2	9.6	14.4]
04	230	4.4	6.5	8.7	13.1]
	277	3.6	5.4	7.2	10.8	Ī
	115	8.7	13.1	17.4	26.1	1
06	208	4.8	7.2	9.6	14.4	1
00	230	4.4	6.5	8.7	13.1	I
	277	3.6	5.4	7.2	10.8]

		UNIT DATA				3 R(OW CHILLED W	ATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	233	(1) 1/50	0.4	45	55.6 / 54	6.2	5.0	45 / 55	1.2	4.6
3	307	(1) 1/20	0.6	60	55 / 53.3	8.7	6.8	45 / 55	1.7	7.8
4	448	(1) 1/20	0.8	70	57 / 55	10.6	8.9	45 / 55	2.1	2.2
6	562	(1) 1/20	0.8	80	55.1 / 53.5	15.7	12.4	45 / 55	3.1	5.0
8	657	(1) 1/10	1.1	114	55.4 / 53.6	18.1	14.2	45 / 54.9	3.6	6.4
10	854	(2) 1/20	1.5	132	54.7 / 53	25.0	19.2	45 / 55.1	4.9	13.8
12	902	(2) 1/20	1.5	142	54.5 / 53	26.3	20.4	45 / 55	5.2	5.9
2	233	(1) 1/50	0.4	45	54.9 / 53.3	6.6	5.2	42 / 54.1	1.1	3.9
3	307	(1) 1/20	0.6	60	53.8 / 52.2	9.6	7.2	42 / 54	1.6	7.3
4	448	(1) 1/20	0.8	70	53.7 / 52	14.2	10.5	42 / 54	2.4	14.4
6	562	(1) 1/20	0.8	80	54.1 / 52.5	17.1	13.0	42 / 54	2.8	4.4
8	657	(1) 1/10	1.1	114	54.4 / 52.6	19.8	15.0	42 / 54	3.3	5.7
10	854	(2) 1/20	1.5	132	53.3 / 51.6	27.9	20.5	42 / 54	4.6	12.5
12	902	(2) 1/20	1.5	142	53.3 / 51.9	29.0	21.6	42 / 54	4.8	5.2
2	233	(1) 1/50	0.4	45	56.7 / 54.9	5.6	4.7	42 / 56	0.8	2.4
3	307	(1) 1/20	0.6	60	55.3 / 53.6	8.5	6.7	42 / 56.1	1.2	4.9
4	448	(1) 1/20	0.8	70	54.7 / 52.9	13.2	10.0	42 / 55.9	1.9	10.1
6	562	(1) 1/20	0.8	80	55.4 / 53.8	15.2	12.1	42 / 55.9	2.2	2.8
8	657	(1) 1/10	1.1	114	55.6 / 53.8	17.8	14.0	42 / 55.9	2.5	3.8
10	854	(2) 1/20	1.5	132	54.4 / 52.6	25.7	19.5	42 / 56.1	3.6	8.4
12	902	(2) 1/20	1.5	142	53.5 / 52	28.7	21.4	42 / 56.1	4.1	11.1
2	233	(1) 1/50	0.4	45	59.2 / 56.8	4.4	4.1	42 / 58	0.5	1.2
3	307	(1) 1/20	0.6	60	56.7 / 54.8	7.4	6.2	42 / 58	0.9	3.3
4	448	(1) 1/20	0.8	70	55.9 / 53.9	12.0	9.5	42 / 58	1.5	7.6
6	562	(1) 1/20	0.8	80	57.1 / 55.2	13.1	11.1	42 / 58	1.6	1.7
8	657	(1) 1/10	1.1	114	57.2 / 55.1	15.4	12.9	42 / 58	1.9	2.4
10	854	(2) 1/20	1.5	132	55.5 / 53.7	23.4	18.4	42 / 58	2.9	5.9
12	902	(2) 1/20	1.5	142	54.6 / 53	26.4	20.3	42 / 58.1	3.3	8.0

NOTE: Based on 75°F DB EAT, 63°F WB, and 3 row cooling coil. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA	l l			4	ROW CHILLED	WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	228	(1) 1/50	0.4	45	52.5 / 51.6	7.5	5.7	45 / 55	1.5	7.8
3	297	(1) 1/20	0.6	60	52 / 51.1	10.1	7.6	45 / 54.9	2.0	12.0
4	426	(1) 1/20	0.8	70	53.6 / 52.6	12.9	10.1	45 / 55.1	2.5	4.0
6	543	(1) 1/20	0.8	80	52.2 / 51.3	18.3	13.7	45 / 55	3.6	8.2
8	620	(1) 1/10	1.1	114	52.5 / 51.5	20.6	15.5	45 / 55.1	4.1	9.9
10	821	(2) 1/20	1.5	132	52.9 / 51.8	26.4	20.1	45 / 55.1	5.2	6.6
12	848	(2) 1/20	1.5	142	52 / 51.1	28.8	21.6	45 / 55	5.8	8.4
2	228	(1) 1/50	0.4	45	51.1 / 50.3	8.3	6.0	42 / 53.9	1.4	7.3
3	297	(1) 1/20	0.6	60	50.3 / 49.5	11.3	8.1	42 / 53.9	1.9	11.4
4	426	(1) 1/20	0.8	70	52.5 / 51.5	14.1	10.6	42 / 54	2.3	3.6
6	562	(1) 1/20	0.8	80	54.1 / 52.5	17.1	13.0	42 / 54	2.8	4.4
8	620	(1) 1/10	1.1	114	50.9 / 50	22.9	16.5	42 / 54.1	3.8	9.2
10	821	(2) 1/20	1.5	132	51.4 / 50.4	29.4	21.4	42 / 53.9	4.9	6.0
12	848	(2) 1/20	1.5	142	50.4 / 49.6	32.2	23.1	42 / 54	5.3	7.8
2	228	(1) 1/50	0.4	45	52.7 / 51.8	7.4	5.6	42 / 55.9	1.1	5.0
3	297	(1) 1/20	0.6	60	51.6 / 50.7	10.4	7.7	42 / 55.9	1.5	8.9
4	426	(1) 1/20	0.8	70	54.2 / 53.2	12.3	9.8	42 / 56	1.7	2.2
6	543	(1) 1/20	0.8	80	52 / 51.1	18.5	13.8	42 / 56.1	2.6	5.1
8	620	(1) 1/10	1.1	114	52.1 / 51.2	21.1	15.7	42 / 56.1	3.0	6.5
10	821	(2) 1/20	1.5	132	51.2 / 50.2	29.8	21.6	42 / 56.1	4.2	13.8
12	848	(2) 1/20	1.5	142	51.7 / 50.8	29.5	21.8	42 / 56	4.2	5.1
2	228	(1) 1/50	0.4	45	54.4 / 53.4	6.4	5.2	42 / 58	0.8	3.2
3	297	(1) 1/20	0.6	60	53.1 / 52.1	9.4	7.2	42 / 58	1.2	6.3
4	426	(1) 1/20	0.8	70	52.4 / 51.4	14.2	10.6	42 / 58	1.8	12.6
6	543	(1) 1/20	0.8	80	53.4 / 52.4	16.6	13.0	42 / 58	2.1	3.5
8	620	(1) 1/10	1.1	114	53.4 / 52.3	19.2	14.8	42 / 57.9	2.4	4.6
10	821	(2) 1/20	1.5	132	52.1 / 51.2	27.9	20.7	42 / 57.9	3.5	10.5
12	848	(2) 1/20	1.5	142	51.3 / 50.5	30.3	22.2	42 / 58	3.8	13.0

NOTE: Based on 75°F DB EAT, 63°F WB, and 4 row cooling coil. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

	U	NIT DATA				3 ROW CH	IILLED WATER	COIL			1 ROW HOT V	VATER COI	IL
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	LAT DB (°F)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	228	(1) 1/50	0.4	45	55.6 / 54	6.0	4.9	1.2	4.4	95.3	6.3	0.3	0.12
3	297	(1) 1/20	0.6	60	54.8 / 53.2	8.5	6.6	1.7	7.7	97.8	9.0	0.5	0.21
4	426	(1) 1/20	0.8	70	56.7 / 54.9	10.2	8.6	2	2.1	98.4	13.2	0.7	0.41
6	543	(1) 1/20	0.8	80	54.9 / 53.4	15.3	12.1	3	4.8	100.9	18.3	0.9	0.96
8	620	(1) 1/10	1.1	114	55.1 / 53.4	17.4	13.6	3.5	6.1	100.1	20.3	1	1.22
10	821	(2) 1/20	1.5	132	54.4 / 52.8	24.4	18.7	4.9	13.5	101.4	28.1	1.4	2.87
12	848	(2) 1/20	1.5	142	54.2 / 52.8	25.2	19.5	5	5.5	103.3	30.7	1.6	3.84

NOTE: Based on 70°F EAT, 180°F EWT, 40°F temperature drop. Cooling coil data based on 75°F DB EAT, 63°F WB, 45°F EWT, 55°F LWT. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA				3 RO	W CHILLED W	ATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	233	(1) 1/50	0.4	45	56.1 / 54.4	7.5	5.6	45 / 55	1.5	5.8
3	307	(1) 1/20	0.6	60	55.6 / 53.9	10.3	7.6	45 / 55	2.0	9.0
4	448	(1) 1/20	0.8	70	57.4 / 55.5	13.0	10.2	45 / 54.9	2.6	3.1
6	562	(1) 1/20	0.8	80	55.7 / 54	18.6	13.9	45 / 55	3.7	6.3
8	657	(1) 1/10	1.1	114	56.2 / 54.3	21.2	15.9	45 / 55	4.2	8.0
10	854	(2) 1/20	1.5	132	55.9 / 54.2	27.9	20.9	45 / 55	5.6	5.7
12	902	(2) 1/20	1.5	142	55.1 / 53.5	31.1	22.9	45 / 55	6.2	7.7
2	233	(1) 1/50	0.4	45	55.3 / 53.6	7.9	5.9	42 / 54.1	1.3	5.1
3	307	(1) 1/20	0.6	60	54.2 / 52.6	11.3	8.1	42 / 53.9	1.9	8.6
4	448	(1) 1/20	0.8	70	56.9 / 55	13.6	10.5	42 / 54	2.2	2.5
6	562	(1) 1/20	0.8	80	54.5 / 52.9	20.3	14.6	42 / 54.1	3.3	5.6
8	657	(1) 1/10	1.1	114	55 / 53.2	23.2	16.7	42 / 54	3.8	7.0
10	854	(2) 1/20	1.5	132	54.8 / 53.2	30.2	21.9	42 / 54	5.0	5.0
12	902	(2) 1/20	1.5	142	53.8 / 52.3	34.0	24.2	42 / 54	5.7	6.7
2	233	(1) 1/50	0.4	45	57 / 55.2	6.9	5.4	42 / 56.1	1.0	3.3
3	307	(1) 1/20	0.6	60	55.7 / 53.9	10.2	7.6	42 / 56	1.5	6.4
4	448	(1) 1/20	0.8	70	55.5 / 53.6	15.4	11.2	42 / 56	2.2	12.4
6	562	(1) 1/20	0.8	80	55.9 / 54.2	18.4	13.8	42 / 56	2.6	3.8
8	657	(1) 1/10	1.1	114	56.2 / 54.3	21.2	15.8	42 / 56	3.0	5.0
10	854	(2) 1/20	1.5	132	55 / 53.2	30.1	21.8	42 / 56	4.3	10.7
12	902	(2) 1/20	1.5	142	54 / 52.5	33.6	23.9	42 / 56	4.8	14.9
2	233	(1) 1/50	0.4	45	58.9 / 56.9	5.9	4.9	42 / 58	0.7	2.0
3	307	(1) 1/20	0.6	60	57.2 / 55.3	9.1	7.1	42 / 58.1	1.1	4.5
4	448	(1) 1/20	0.8	70	56.5 / 54.5	14.3	10.7	42 / 58	1.8	9.5
6	562	(1) 1/20	0.8	80	57.4 / 55.5	16.3	12.8	42 / 57.9	2.0	2.5
8	657	(1) 1/10	1.1	114	57.6 / 55.6	18.9	14.8	42 / 58	2.4	3.3
10	854	(2) 1/20	1.5	132	56 / 54.1	28.0	20.8	42 / 58	3.5	7.9
12	902	(2) 1/20	1.5	142	55.1 / 53.4	31.3	22.9	42 / 57.9	3.9	10.3

NOTE: Based on 78°F DB EAT, 65°F WB, and 3 row cooling coil. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA				4 R	OW CHILLED V	WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	228	(1) 1/50	0.4	45	52.7 / 51.8	8.9	6.4	45 / 55	1.8	9.2
3	297	(1) 1/20	0.6	60	54.8 / 53.9	9.9	7.6	45 / 55.1	2.0	2.4
4	426	(1) 1/20	0.8	70	53.9 / 52.8	15.4	11.4	45 / 55.1	3.0	5.2
6	543	(1) 1/20	0.8	80	52.5 / 51.6	21.5	15.4	45 / 55	4.3	10.4
8	620	(1) 1/10	1.1	114	52.8 / 51.8	24.1	17.3	45 / 55	4.8	13.4
10	821	(2) 1/20	1.5	132	53.2 / 52.2	31.2	22.5	45 / 55	6.2	8.4
12	848	(2) 1/20	1.5	142	52.3 / 51.4	33.8	24.1	45 / 55	6.7	11.1
2	228	(1) 1/50	0.4	45	51.3 / 50.4	9.7	6.7	42 / 54	1.6	8.6
3	297	(1) 1/20	0.6	60	50.6 / 49.8	13.1	9.0	42 / 54	2.2	13.6
4	426	(1) 1/20	0.8	70	52.7 / 51.7	16.7	11.9	42 / 54.1	2.8	4.6
6	543	(1) 1/20	0.8	80	50.9 / 50	23.6	16.3	42 / 54	3.9	9.1
8	620	(1) 1/10	1.1	114	51.2 / 50.3	26.6	18.4	42 / 54	4.4	11.6
10	821	(2) 1/20	1.5	132	51.7 / 50.7	34.2	23.9	42 / 54	5.7	7.4
12	848	(2) 1/20	1.5	142	50.6 / 49.8	37.3	25.7	42 / 54	6.2	9.6
2	228	(1) 1/50	0.4	45	52.8 / 51.9	8.8	6.4	42 / 56	1.3	6.4
3	297	(1) 1/20	0.6	60	51.8 / 50.9	12.3	8.6	42 / 56	1.7	10.6
4	426	(1) 1/20	0.8	70	54.4 / 53.3	14.9	11.2	42 / 56.1	2.1	3.0
6	543	(1) 1/20	0.8	80	52.1 / 51.2	22.0	15.6	42 / 56	3.1	6.7
8	620	(1) 1/10	1.1	114	52.3 / 51.3	24.9	17.6	42 / 56	3.6	8.5
10	821	(2) 1/20	1.5	132	53.1 / 52	31.5	22.7	42 / 56	4.5	5.1
12	848	(2) 1/20	1.5	142	52 / 51	34.7	24.5	42 / 56.1	4.9	6.7
2	228	(1) 1/50	0.4	45	54.4 / 53.5	7.9	6.0	42 / 58	1.0	4.4
3	297	(1) 1/20	0.6	60	53.2 / 52.2	11.2	8.2	42 / 58	1.4	8.1
4	426	(1) 1/20	0.8	70	52.8 / 51.7	16.7	11.9	42 / 58	2.1	15.0
6	543	(1) 1/20	0.8	80	53.5 / 52.5	20.1	14.8	42 / 58	2.5	4.8
8	620	(1) 1/10	1.1	114	53.7 / 52.6	22.8	16.7	42 / 58.1	2.8	6.0
10	821	(2) 1/20	1.5	132	52.5 / 51.5	32.6	23.2	42 / 58	4.1	12.9
12	848	(2) 1/20	1.5	142	53.2 / 52.3	31.9	23.3	42 / 58	4.0	4.6

NOTE: Based on 78°F DB EAT, 65°F WB, and 4 row cooling coil. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA				3 ROW CHI	LLED WATER O	OIL		1	ROW HOT W	ATER COIL	_
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	LAT DB (°F)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	228	(1) 1/50	0.4	45	56 / 54.4	7.3	5.5	1.5	5.7	95.3	6.3	0.3	0.12
3	297	(1) 1/20	0.6	60	55.4 / 53.7	10.1	7.4	2	8.7	97.8	9.0	0.5	0.21
4	426	(1) 1/20	0.8	70	57.3 / 55.4	12.4	9.8	2.5	2.9	98.4	13.2	0.7	0.41
6	543	(1) 1/20	0.8	80	55.4 / 53.8	18.2	13.6	3.6	6.2	100.9	18.3	0.9	0.96
8	620	(1) 1/10	1.1	114	55.8 / 54	20.5	15.2	4.1	7.5	100.1	20.3	1	1.22
10	821	(2) 1/20	1.5	132	55.7 / 54	27.2	20.3	5.4	5.6	101.4	28.1	1.4	2.87
12	848	(2) 1/20	1.5	142	54.8 / 53.3	29.7	21.8	5.9	6.9	103.3	30.7	1.6	3.84

NOTE: Based on 70°F EAT, 180°F EWT, 40°F temperature drop. Cooling coil data based on 78°F DB EAT, 65°F WB, 45°F EWT, 55°F LWT. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA				3 RC	W CHILLED W	ATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	233	(1) 1/50	0.4	45	55.6 / 54.2	5.3	4.2	45 / 55	1.1	3.7
3	307	(1) 1/20	0.6	60	54.7 / 53.4	7.7	5.9	45 / 55	1.5	6.8
4	448	(1) 1/20	0.8	70	54.6 / 53.2	11.5	8.6	45 / 55	2.3	13.6
6	562	(1) 1/20	0.8	80	54.9 / 53.5	13.8	10.7	45 / 55	2.8	4.2
8	657	(1) 1/10	1.1	114	55.1 / 53.6	16.0	12.3	45 / 55	3.2	5.4
10	854	(2) 1/20	1.5	132	54.2 / 52.9	22.5	16.8	45 / 55	4.5	11.7
12	902	(2) 1/20	1.5	142	54.3 / 53	23.4	17.7	45 / 55	4.7	4.9
2	233	(1) 1/50	0.4	45	54.9 / 53.6	5.7	4.4	42 / 54	0.9	3.2
3	307	(1) 1/20	0.6	60	53.6 / 52.3	8.5	6.2	42 / 54	1.4	6.3
4	448	(1) 1/20	0.8	70	53.3 / 51.9	12.9	9.3	42 / 54	2.1	12.1
6	562	(1) 1/20	0.8	80	53.8 / 52.6	15.3	11.3	42 / 54	2.5	3.7
8	657	(1) 1/10	1.1	114	54.2 / 52.7	17.6	13.0	42 / 54	2.9	4.7
10	854	(2) 1/20	1.5	132	52.9 / 51.6	25.3	18.0	42 / 54	4.2	10.4
12	902	(2) 1/20	1.5	142	52.2 / 51	28.1	19.7	42 / 54	4.6	14.1
2	233	(1) 1/50	0.4	45	57.1 / 55.5	4.5	3.8	42 / 56	0.6	1.6
3	307	(1) 1/20	0.6	60	55.2 / 53.7	7.4	5.7	42 / 56	1.1	4.1
4	448	(1) 1/20	0.8	70	54.5 / 52.9	11.7	8.7	42 / 56	1.7	9.0
6	562	(1) 1/20	0.8	80	55.5 / 54.1	13.0	10.3	42 / 56	1.9	2.2
8	657	(1) 1/10	1.1	114	55.6 / 54	15.3	11.9	42 / 56	2.2	2.9
10	854	(2) 1/20	1.5	132	54.1 / 52.7	22.9	16.9	42 / 56	3.3	7.2
12	902	(2) 1/20	1.5	142	53.3 / 52.1	25.7	18.6	42 / 56.1	3.6	9.4
2	233	(1) 1/50	0.4	45	58.4 / 56.4	3.9	3.5	42 / 58	0.5	1.0
3	307	(1) 1/20	0.6	60	56.9 / 55.2	6.1	5.1	42 / 58	0.8	2.4
4	448	(1) 1/20	0.8	70	55.8 / 54.2	10.3	8.0	42 / 58.1	1.3	6.1
6	562	(1) 1/20	0.8	80	54.2 / 52.8	14.9	11.1	42 / 58	1.9	12.5
8	657	(1) 1/10	1.1	114	57.2 / 55.4	12.8	10.7	42 / 57.9	1.6	1.7
10	854	(2) 1/20	1.5	132	55.3 / 53.8	20.3	15.7	42 / 57.9	2.5	4.7
12	902	(2) 1/20	1.5	142	54.4 / 53.1	23.2	17.5	42 / 57.9	2.9	6.5

NOTE: Based on 72°F DB EAT, 62°F WB, and 3 row cooling coil. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA				4 RC	W CHILLED W	ATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	228	(1) 1/50	0.4	45	52.6 / 51.9	6.6	4.9	45 / 55	1.3	6.7
3	297	(1) 1/20	0.6	60	51.9 / 51.2	9.1	6.6	45 / 55	1.8	10.7
4	426	(1) 1/20	0.8	70	53.6 / 52.8	11.3	8.7	45 / 55	2.2	3.3
6	543	(1) 1/20	0.8	80	52.1 / 51.4	16.4	12.0	45 / 55	3.3	7.2
8	620	(1) 1/10	1.1	114	52.3 / 51.5	18.6	13.5	45 / 55	3.7	8.7
10	821	(2) 1/20	1.5	132	52.8 / 52	23.6	17.4	45 / 55	4.7	5.5
12	848	(2) 1/20	1.5	142	51.9 / 51.2	26.0	18.9	45 / 54.9	5.2	7.4
2	228	(1) 1/50	0.4	45	51.2 / 50.5	7.4	5.3	42 / 53.9	1.2	6.3
3	297	(1) 1/20	0.6	60	50.3 / 49.6	10.3	7.1	42 / 54	1.7	10.5
4	426	(1) 1/20	0.8	70	52.6 / 51.9	12.3	9.1	42 / 54.1	2.0	2.9
6	543	(1) 1/20	0.8	80	50.6 / 50	18.4	12.8	42 / 54	3.0	6.6
8	620	(1) 1/10	1.1	114	50.7 / 50	20.9	14.6	42 / 54	3.5	8.4
10	821	(2) 1/20	1.5	132	51.4 / 50.6	26.3	18.7	42 / 54	4.4	4.9
12	848	(2) 1/20	1.5	142	50.5 / 49.8	29.0	20.2	42 / 54.1	4.8	6.5
2	228	(1) 1/50	0.4	45	53 / 52.3	6.4	4.8	42 / 56	0.9	3.9
3	297	(1) 1/20	0.6	60	51.8 / 51.1	9.2	6.6	42 / 56	1.3	7.5
4	426	(1) 1/20	0.8	70	51.3 / 50.5	13.8	9.7	42 / 56	2.0	13.8
6	543	(1) 1/20	0.8	80	52.1 / 51.4	16.4	11.9	42 / 56	2.3	4.2
8	620	(1) 1/10	1.1	114	52.1 / 51.3	18.8	13.6	42 / 55.9	2.7	5.6
10	821	(2) 1/20	1.5	132	51.1 / 50.3	27.0	19.0	42 / 56	3.8	11.9
12	848	(2) 1/20	1.5	142	51.9 / 51.2	26.1	18.9	42 / 56	3.7	4.1
2	228	(1) 1/50	0.4	45	55 / 54.1	5.2	4.3	42 / 57.9	0.7	2.3
3	297	(1) 1/20	0.6	60	53.3 / 52.5	8.1	6.1	42 / 57.9	1.0	5.1
4	426	(1) 1/20	0.8	70	52.6 / 51.7	12.5	9.2	42 / 58	1.6	10.9
6	543	(1) 1/20	0.8	80	53.7 / 52.9	14.3	11.0	42 / 58	1.8	2.7
8	620	(1) 1/10	1.1	114	53.7 / 52.8	16.4	12.5	42 / 58	2.0	3.5
10	821	(2) 1/20	1.5	132	52.3 / 51.5	24.5	17.9	42 / 58	3.0	8.5
12	848	(2) 1/20	1.5	142	51.5 / 50.8	26.9	19.2	42 / 58	3.3	11.1

NOTE: Based on 72°F DB EAT, 62°F WB, and 4 row cooling coil. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

		UNIT DATA				3 ROW CHI	LLED WATER O	OIL		1	ROW HOT W	ATER COIL	-
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	LAT DB (°F)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)
2	228	(1) 1/50	0.4	45	55.4 / 54.1	5.3	4.2	1.1	3.7	95.3	6.3	0.3	0.12
3	297	(1) 1/20	0.6	60	54.6 / 53.3	7.5	5.7	1.5	6.6	97.8	9.0	0.5	0.21
4	426	(1) 1/20	0.8	70	54.4 / 53	11.1	8.3	2.2	12.8	98.4	13.2	0.7	0.41
6	543	(1) 1/20	0.8	80	54.7 / 53.4	13.5	10.4	2.7	4.0	100.9	18.3	0.9	0.96
8	620	(1) 1/10	1.1	114	54.9 / 53.5	15.3	11.7	3	5.0	100.1	20.3	1	1.22
10	821	(2) 1/20	1.5	132	54.1 / 52.8	21.9	16.3	4.4	11.0	101.4	28.1	1.4	2.87
12	848	(2) 1/20	1.5	142	53.3 / 52.1	24.0	17.5	4.8	14.8	103.3	30.7	1.6	3.84

NOTE: Based on 70°F EAT, 180°F EWT, 40°F temperature drop. Cooling coil data based on 72°F DB EAT, 62°F WB, 45°F EWT, 55°F LWT. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'. Fan watts shown at operating conditions. FLA based on motor nameplate.

	ι	JNIT DATA				:	3 ROW CHILLE	WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
02	236	(1) 1/25	0.6	65	54.2 / 52.8	7.0	5.4	45 / 55.1	1.4	5.8
03	336	(1) 1/25	0.6	62	56.6 / 55	8.0	6.8	45 / 54.9	1.6	1.4
04	452	(1) 1/25	0.6	62	55.1 / 53.6	12.4	10.0	45 / 55	2.5	3.2
06	615	(2) 1/25	1.2	127	53.7 / 52.4	19.0	14.5	45 / 55	3.8	7.8
02	236	(1) 1/25	0.6	65	53 / 51.7	7.7	5.7	42 / 54	1.3	5.3
03	336	(1) 1/25	0.6	62	56.7 / 55.1	7.9	6.8	42 / 54.1	1.3	1.0
04	452	(1) 1/25	0.6	62	54.1 / 52.7	13.5	10.4	42 / 54	2.2	2.8
06	615	(2) 1/25	1.2	127	52.3 / 51	21.1	15.4	42 / 54	3.5	7.3
02	236	(1) 1/25	0.6	65	54.6 / 53.2	6.8	5.3	42 / 56	1.0	3.4
03	336	(1) 1/25	0.6	62	58.7 / 56.6	6.5	6.0	42 / 56	0.9	0.5
04	452	(1) 1/25	0.6	62	55.8 / 54.2	11.7	9.6	42 / 55.9	1.7	1.7
06	615	(2) 1/25	1.2	127	53.5 / 52.2	19.3	14.6	42 / 55.9	2.8	4.9
02	236	(1) 1/25	0.6	65	56.4 / 54.8	5.7	4.8	42 / 58	0.7	2.1
03	336	(1) 1/25	0.6	62	59.4 / 57	6.1	5.8	42 / 58	0.8	0.4
04	452	(1) 1/25	0.6	62	58.2 / 56.1	9.3	8.4	42 / 58	1.2	0.9
06	615	(2) 1/25	1.2	127	54.9 / 53.5	17.2	13.6	42 / 58	2.1	3.2

	ι	JNIT DATA				4	4 ROW CHILLEI	O WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
02	230	(1) 1/25	0.6	65	51.2 / 50.5	8.2	6.1	45 / 55	1.6	9.4
03	328	(1) 1/25	0.6	62	53.2 / 52.5	10.0	7.9	45 / 55	2.0	2.7
04	438	(1) 1/25	0.6	62	54.4 / 53.6	12.1	10.0	45 / 55.1	2.4	1.3
06	602	(2) 1/25	1.2	127	52.4 / 51.6	19.7	15.0	45 / 55	3.9	3.7
02	230	(1) 1/25	0.6	65	49.5 / 48.9	9.1	6.5	42 / 53.9	1.5	9.0
03	328	(1) 1/25	0.6	62	52.2 / 51.5	10.9	8.3	42 / 53.9	1.8	2.3
04	438	(1) 1/25	0.6	62	53.8 / 53	12.8	10.2	42 / 54	2.1	1.1
06	602	(2) 1/25	1.2	127	51.1 / 50.3	21.7	15.9	42 / 54	3.6	3.2
02	230	(1) 1/25	0.6	65	51/50.4	8.3	6.1	42 / 56	1.2	6.3
03	328	(1) 1/25	0.6	62	54.6 / 53.7	9.0	7.4	42 / 56	1.3	1.2
04	438	(1) 1/25	0.6	62	56.8 / 55.5	9.7	8.8	42 / 56	1.4	0.5
06	602	(2) 1/25	1.2	127	52.7 / 52	19.2	14.8	42 / 56	2.7	2.0
02	230	(1) 1/25	0.6	65	52.5 / 51.8	7.4	5.7	42 / 58	0.9	4.3
03	328	(1) 1/25	0.6	62	56.6 / 55.4	7.4	6.7	42 / 58	0.9	0.7
04	438	(1) 1/25	0.6	62	57.5 / 56	9.2	8.4	42 / 58	1.1	0.3
06	602	(2) 1/25	1.2	127	54.5 / 53.6	16.6	13.6	42 / 58	2.1	1.2

NOTE: Based on 75°F DB EAT, 63°F WB. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'.

	UN	IIT DATA				3 ROW CH	ILLED WATER	COIL		1 ROW HOT WATER COIL				
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	LAT DB (°F)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	
02	230	(1) 1/25	0.6	65	54 / 52.7	6.9	5.4	1.4	5.8	99.4	7.3	0.4	0.16	
03	328	(1) 1/25	0.6	62	56.7 / 55.1	7.7	6.6	1.5	1.3	100.4	10.8	0.6	0.29	
04	438	(1) 1/25	0.6	62	55 / 53.6	12.1	9.7	2.4	3.1	101.7	15.1	0.8	0.62	
06	602	(2) 1/25	1.2	127	53.5 / 52.2	18.8	14.3	3.8	7.8	103.7	22.1	1.1	1.66	

NOTE: Based on 70°F EAT, 180°F EWT, 40°F temperature drop. Cooling coil data based on 75°F DB EAT, 63°F WB, 45°F EWT, 55°F LWT. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'.

	ι	JNIT DATA			3 ROW CHILLED WATER COIL							
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)		
02	236	(1) 1/25	0.6	65	54.4 / 53.1	8.4	6.2	45 / 55	1.7	7.2		
03	336	(1) 1/25	0.6	62	57 / 55.4	9.8	7.8	45 / 55	2.0	1.9		
04	452	(1) 1/25	0.6	62	55.5 / 54	15.0	11.3	45 / 55	3.0	4.3		
06	615	(2) 1/25	1.2	127	54.2 / 52.8	22.3	16.2	45 / 55	4.4	10.2		
02	236	(1) 1/25	0.6	65	53.2 / 51.9	9.1	6.5	42 / 53.9	1.5	6.7		
03	336	(1) 1/25	0.6	62	56.6 / 55.1	10.1	7.9	42 / 54.1	1.7	1.5		
04	452	(1) 1/25	0.6	62	54.5 / 53	16.2	11.8	42 / 54	2.7	3.7		
06	615	(2) 1/25	1.2	127	52.8 / 51.4	24.5	17.2	42 / 54	4.1	8.7		
02	236	(1) 1/25	0.6	65	54.8 / 53.4	8.2	6.1	42 / 56	1.2	4.6		
03	336	(1) 1/25	0.6	62	59.6 / 57.6	7.7	6.8	42 / 56.1	1.1	0.7		
04	452	(1) 1/25	0.6	62	56.1 / 54.6	14.3	11.0	42 / 56	2.0	2.4		
06	615	(2) 1/25	1.2	127	53.9 / 52.5	22.8	16.4	42 / 55.9	3.3	6.5		
02	236	(1) 1/25	0.6	65	56.5 / 55	7.2	5.6	42 / 58	0.9	3.0		
03	336	(1) 1/25	0.6	62	60.6 / 58.3	7.0	6.4	42 / 58	0.9	0.5		
04	452	(1) 1/25	0.6	62	57.9 / 56.2	12.2	10.0	42 / 58	1.5	1.4		
06	615	(2) 1/25	1.2	127	55.3 / 53.8	20.7	15.5	42 / 58	2.6	4.4		

	ι	JNIT DATA				4	4 ROW CHILLED	O WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
02	230	(1) 1/25	0.6	65	51.3 / 50.7	9.6	6.8	45 / 55	1.9	10.6
03	328	(1) 1/25	0.6	62	53.4 / 52.6	12.1	8.9	45 / 55	2.4	3.5
04	438	(1) 1/25	0.6	62	54.4 / 53.6	15.0	11.4	45 / 55	3.0	1.9
06	602	(2) 1/25	1.2	127	52.6 / 51.7	23.5	17.0	45 / 55	4.7	5.0
02	230	(1) 1/25	0.6	65	49.6 / 49	10.6	7.2	42 / 54.1	1.7	10.4
03	328	(1) 1/25	0.6	62	52.2 / 51.5	13.1	9.4	42 / 53.9	2.2	3.1
04	438	(1) 1/25	0.6	62	53.7 / 52.9	15.8	11.8	42 / 54	2.6	1.5
06	602	(2) 1/25	1.2	127	51.2 / 50.4	25.6	17.9	42 / 54	4.2	4.3
02	230	(1) 1/25	0.6	65	51/50.3	9.8	6.9	42 / 56	1.4	7.9
03	328	(1) 1/25	0.6	62	54.3 / 53.5	11.3	8.6	42 / 56.1	1.6	1.8
04	438	(1) 1/25	0.6	62	56.2 / 55.2	13.0	10.6	42 / 56	1.9	0.8
06	602	(2) 1/25	1.2	127	52.7 / 51.9	23.3	16.9	42 / 56	3.3	2.8
02	230	(1) 1/25	0.6	65	52.4 / 51.7	9.0	6.5	42 / 57.9	1.1	5.8
03	328	(1) 1/25	0.6	62	56.7 / 55.7	9.3	7.7	42 / 58	1.2	1.0
04	438	(1) 1/25	0.6	62	58.6 / 57.2	10.5	9.4	42 / 58	1.3	0.4
06	602	(2) 1/25	1.2	127	54.4 / 53.6	20.6	15.7	42 / 58	2.6	1.8

NOTE: Based on 78°F DB EAT, 65°F WB. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'.

	UN	IIT DATA			3 ROW CHILLED WATER COIL						1 ROW HOT WATER COIL			
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	LAT DB (°F)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	
02	230	(1) 1/25	0.6	65	54.3 / 53	8.2	6.0	1.6	7.1	99.4	7.3	0.4	0.16	
03	328	(1) 1/25	0.6	62	56.8 / 55.3	9.7	7.7	1.9	1.9	100.4	10.8	0.6	0.29	
04	438	(1) 1/25	0.6	62	55.4 / 53.9	14.7	11.0	2.9	4.1	101.7	15.1	0.8	0.62	
06	602	(2) 1/25	1.2	127	54.1 / 52.8	22.0	15.9	4.4	9.9	103.7	22.1	1.1	1.66	

NOTE: Based on 70°F EAT, 180°F EWT, 40°F temperature drop. Cooling coil data based on 78°F DB EAT, 65°F WB, 45°F EWT, 55°F LWT. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit.

	ι	JNIT DATA					3 ROW CHILLEI	O WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
02	236	(1) 1/25	0.6	65	54 / 52.9	6.2	4.7	45 / 55	1.2	5.0
03	336	(1) 1/25	0.6	62	56.8 / 55.4	6.5	5.6	45 / 54.9	1.3	1.0
04	452	(1) 1/25	0.6	62	54.9 / 53.7	10.9	8.5	45 / 55	2.2	2.6
06	615	(2) 1/25	1.2	127	53.5 / 52.4	16.9	12.6	45 / 55.1	3.3	6.7
02	236	(1) 1/25	0.6	65	53 / 51.9	6.8	5.0	42 / 54	1.1	4.4
03	336	(1) 1/25	0.6	62	57.4 / 55.8	6.1	5.4	42 / 54	1.0	0.6
04	452	(1) 1/25	0.6	62	54.1 / 53	11.8	8.9	42 / 54	2.0	2.2
06	615	(2) 1/25	1.2	127	52.2 / 51.2	18.9	13.5	42 / 54.1	3.1	6.1
02	236	(1) 1/25	0.6	65	54.8 / 53.6	5.7	4.5	42 / 56	0.8	2.6
03	336	(1) 1/25	0.6	62	58 / 56.2	5.8	5.2	42 / 56	0.8	0.4
04	452	(1) 1/25	0.6	62	56.2 / 54.9	9.5	7.9	42 / 56	1.3	1.1
06	615	(2) 1/25	1.2	127	53.6 / 52.5	16.9	12.5	42 / 56	2.4	3.9
02	236	(1) 1/25	0.6	65	57.2 / 55.7	4.4	3.8	42 / 58	0.5	1.3
03	336	(1) 1/25	0.6	62	58.8 / 56.8	5.3	4.9	42 / 58.1	0.7	0.3
04	452	(1) 1/25	0.6	62	58.7 / 56.7	7.1	6.6	42 / 58	0.9	0.5
06	615	(2) 1/25	1.2	127	55.1 / 53.9	14.6	11.5	42 / 58	1.8	2.4

	ι	JNIT DATA				4	4 ROW CHILLED	WATER COIL		
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	EWT/LWT (°F)	FLUID FLOW (GPM)	FLUID PD (FT.)
02	230	(1) 1/25	0.6	65	51.3 / 50.8	7.3	5.3	45 / 55	1.5	8.3
03	328	(1) 1/25	0.6	62	53.4 / 52.8	8.7	6.7	45 / 55	1.7	2.1
04	438	(1) 1/25	0.6	62	54.6 / 53.9	10.3	8.4	45 / 54.9	2.1	1.0
06	602	(2) 1/25	1.2	127	52.5 / 51.8	17.5	13.0	45 / 55	3.5	3.1
02	230	(1) 1/25	0.6	65	49.6 / 49.1	8.3	5.7	42 / 53.9	1.4	7.9
03	328	(1) 1/25	0.6	62	52.8 / 52.2	9.3	7.0	42 / 54.1	1.5	1.7
04	438	(1) 1/25	0.6	62	54.5 / 53.8	10.5	8.5	42 / 53.9	1.7	0.7
06	602	(2) 1/25	1.2	127	51.2 / 50.6	19.4	13.8	42 / 54	3.2	2.7
02	230	(1) 1/25	0.6	65	51.2 / 50.7	7.4	5.3	42 / 55.9	1.1	5.3
03	328	(1) 1/25	0.6	62	55.5 / 54.7	7.0	6.0	42 / 56	1.0	0.8
04	438	(1) 1/25	0.6	62	56.3 / 55.3	8.6	7.6	42 / 56	1.2	0.4
06	602	(2) 1/25	1.2	127	53.1 / 52.5	16.5	12.6	42 / 56	2.3	1.5
02	230	(1) 1/25	0.6	65	53.1 / 52.5	6.3	4.8	42 / 58	0.8	3.2
03	328	(1) 1/25	0.6	62	56.2 / 55.2	6.6	5.7	42 / 58	0.8	0.5
04	438	(1) 1/25	0.6	62	57.1 / 55.8	8.0	7.2	42 / 58	1.0	0.3
06	602	(2) 1/25	1.2	127	55.5 / 54.6	13.1	11.0	42 / 58	1.6	0.8

NOTE: Based on 72°F DB EAT, 62°F WB. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit.

	UN	IIT DATA				3 ROW CHI	LLED WATER C	OIL		1 ROW HOT WATER COIL				
UNIT SIZE	AIRFLOW (CFM)	MOTOR (HP)	FAN AMPS (FLA)	FAN WATTS	LAT DB/WB (°F)	TOTAL CAPACITY (MBH)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	LAT DB (°F)	SENSIBLE CAPACITY (MBH)	FLUID FLOW (GPM)	FLUID PD (FT.)	
02	230	(1) 1/25	0.6	65	54 / 52.9	6.03	4.6	1.2	4.8	99.4	7.3	0.4	0.16	
03	328	(1) 1/25	0.6	62	57 / 55.6	6.22	5.4	1.2	0.9	100.4	10.8	0.6	0.29	
04	438	(1) 1/25	0.6	62	54.8 / 53.7	10.59	8.3	2.1	2.5	101.7	15.1	0.8	0.62	
06	602	(2) 1/25	1.2	127	53.4 / 52.3	16.75	12.4	3.3	6.7	103.7	22.1	1.1	1.66	

NOTE: Based on 70°F EAT, 180°F EWT, 40°F temperature drop. Cooling coil data based on 72°F DB EAT, 62°F WB, 45°F EWT, 55°F LWT. All selections made at High speed, .05" ESP, 115 V motor, Concealed style of unit, Altitude of 0'.

MOTOR AND FAN DATA

FW PS	C MOTOR	AND FAN	DATA
-------	---------	----------------	------

UNIT	FAN	MOTOR	# OF		115 VOLTS	208-230 VOLTS	277 VOLTS
SIZE	SPEED	H.P. (QTY.)	FANS	WATTS	AMPS	AMPS	AMPS
	High			45			
02	Medium	(1) 1/50	1	35	0.40	0.27	0.21
	Low			28			
	High			60			
03	Medium	(1) 1/20	1	48	0.60	0.40	0.31
	Low			43			
	High			70			
04	Meduim	(1) 1/20	2	61	0.75	0.39	0.42
	Low			58			
	High			80			
06	Medium	(1) 1/20	2	74	0.75	0.39	0.42
	Low			61			
	High			114			
08	Medium	(1) 1/10	2	81	1.10	0.51	0.50
	Low			71			
10	High			132			
10	Medium	(2) 1/20	4	114	1.50	0.78	0.84
	Low			107			
	High			142			
11	Medium	(2) 1/20	4	126	1.50	0.78	0.84
	Low			114			

NOTES:

1. FWX, 3-row coil, no EH, no toe kick, standard throw away panel filter. Fan watts shown at operating conditions supplied for 115V. 2. Data was taken without ductwork.

3. Unit size 04, 06, 08, 10 and 12 data generated at 115v, 230v and 277v.

4. Unit size 02 & 03 data generated with 115v, 240v to 120v transformer(230v line voltage) and 277v to 120v transformer (277v line voltage).

5. FLA based on motor nameplate.

MOTOR AND FAN DATA

FW ECM MOTOR AND FAN DATA

VERTICAL CONCEALED

UNIT	FAN	MOTOR	# OF		115 \	VOLTS	208-23	0 VOLTS	277	VOLTS
SIZE	SPEED	H.P. (QTY.)	# OF FANS	WATTS	FLA	3-PHASE NEUTRAL	FLA	3-PHASE NEUTRAL	FLA	3-PHASE NEUTRAL
02	High	(1) 1/25	1	34	0.7	1.0	0.5	0.8	0.5	0.8
03	High	(1) 1/25	1	48	1.0	1.5	0.8	1.2	0.7	1.0
04	High	(1) 1/25	2	55	1.2	1.7	0.9	1.3	0.9	1.3
06	High	(1) 1/25	2	63	1.4	2.0	1.1	1.6	1.1	1.6
08	High	(1) 1/25	2	83	1.7	2.5	1.3	1.9	1.2	1.7
10	High	(2) 1/25	4	106	2.2	3.2	1.6	2.4	1.6	2.4
12	High	(2) 1/25	4	120	3.0	4.4	2.4	3.4	2.2	3.2

VERTICAL EXPOSED / SLOPED TOP

UNIT	FAN	MOTOR	# OF		115 \	/OLTS	208-23	0 VOLTS	277	VOLTS
SIZE	SPEED	H.P. (QTY.)	FANS	WATTS	FLA	3-Phase Neutral	FLA	3-Phase Neutral	FLA	3-Phase Neutral
02	High	(1) 1/25	1	38	0.7	1.0	0.5	0.8	0.5	0.8
03	High	(1) 1/25	1	48	1.0	1.5	0.7	1.0	0.7	1.0
04	High	(1) 1/25	2	53	1.1	1.6	0.9	1.3	0.9	1.3
06	High	(1) 1/25	2	66	1.4	2.0	1.1	1.6	1.0	1.5
08	High	(1) 1/25	2	93	1.8	2.6	1.3	1.9	1.3	1.9
10	High	(2) 1/25	4	115	2.8	4.0	2.2	3.2	2.2	3.2
12	High	(2) 1/25	4	120	3.0	4.4	2.2	3.2	2.2	3.2

NOTES:

1. Exposed, 3-row coil, no EH, no toe kick, standard throw away panel filter 2. Watts as shown are for .05" ESP, 3 row coil, 115/1/60, 12 FPI, and throwaway filters

3. Motor HP as noted is a nominal rating

4. Data as supplied is for reference only. For project specific operational points see seletion tool report out.

MOTOR AND FAN DATA

	MOTOR H.P. # OF 115 VOLTS 208-230 VOLTS 277 VOLTS											
	FAN SPEED	MOTOR H.P.	# OF	115 \	/OLTS	208-23	0 VOLTS	277 \	/OLTS			
UNIT SIZE	FAN SPEED	(QTY.)	FANS	AMPS	WATTS	AMPS	WATTS	AMPS	WATTS			
	High	1/25		0.6	65.0	0.3	70.0	0.3	81.0			
02	Medium	1/50	1	0.3	42.0	0.2	43.0	0.2	50.0			
	Low	1/100		0.3	28.0	0.2	29.0	0.2	34.0			
	High	1/25		0.6	62.0	0.3	65.0	0.3	68.0			
03	Medium	1/50	2	0.3	30.0	0.2	37.0	0.2	42.0			
	Low	1/100		0.3	25.0	0.2	26.0	0.2	29.0			
	High	1/25		0.6	62.0	0.3	65.0	0.3	68.0			
04	Meduim	1/50	2	0.3	30.0	0.2	37.0	0.2	42.0			
	Low	1/100		0.3	25.0	0.2	26.0	0.2	29.0			
	High	2 @ 1/25		1.2	127.0	0.6	135.0	0.6	149.0			
06	Medium	2 @ 1/50	3	0.6	72.0	0.4	80.0	0.4	92.0			
	Low	2 @ 1/100		0.6	53.0	0.4	55.0	0.4	63.0			

FL MOTOR AND FAN DATA

NOTES:

1. FWX, 3-row coil, no EH, no toe kick, standard throw away panel filter. Fan watts shown at operating conditions supplied for 115V. 2. Data was taken without ductwork.

SOUND DATA

				OUND					
					TOTAL S	OUND POW	ER LEVEL		
UNIT SIZE	FAN SPEED	SCFM		00	TAVE BAND	/ CENTER FI	REQUENCY	(HZ)	
			125	250	500	1000	2000	4000	8000
	High	233	58	63	60	53	48	43	35
02	Medium	190	48	52	46	43	34	25	26
	Low	149	42	45	31	28	20	23	26
	High	321	57	60	55	52	47	41	34
03	Medium	280	54	56	52	48	42	35	28
	Low	246	49	52	47	43	36	27	27
	High	457	59	62	63	55	48	44	36
04	Medium	420	56	58	59	51	44	38	30
	Low	334	49	55	48	41	32	25	28
	High	570	59	61	67	54	47	42	33
06	Medium	492	55	58	65	50	42	36	28
	Low	362	48	62	48	39	29	23	26
	High	633	65	67	64	58	52	48	41
08	Medium	549	61	62	62	54	47	42	35
	Low	436	57	55	55	46	37	30	28
	High	836	61	63	68	58	51	46	37
10	Medium	792	59	62	67	56	49	43	35
	Low	697	55	57	65	51	43	37	29
	High	978	62	64	65	56	50	44	35
12	Medium	888	60	62	65	54	47	41	32
	Low	697	54	56	60	46	38	30	27

FW SOUND DATA

NOTES:

1. Sound data tested in accordance with AHRI-350-2008.

2. Sound levels expressed in decibels, dB RE: 1 x 10-12 watts.

3. Total sound power level data based on exposed cabinet model with fan CFM at corresponding motor tap with 115/1/60 volt motor, 3 row coil, 1" throwaway filter, 0.0" external static pressure and standard rated internal pressure losses.

					TOTAL	SOUND POWE	R LEVEL		
UNIT SIZE	FAN SPEED	SCFM			OCTAVE BANK	D / CENTER FR	EQUENCY (HZ)		
			2/125	3/250	4/500	5/1000	6/2000	7/4000	8/8000
	High	250	57	64	59	57	52	52	42
02	Medium	185	51	58	52	49	47	43	31
	Low	140	47	51	45	42	40	32	26
	High	360	59	59	57	53	47	41	36
03	Medium	300	52	56	53	48	43	36	34
	Low	250	51	49	46	40	33	27	25
	High	485	54	60	56	52	48	43	37
04	Medium	365	50	54	49	45	40	33	31
	Low	255	43	47	40	37	31	23	25
	High	675	59	64	59	58	53	47	43
06	Medium	500	53	57	54	49	44	37	32
	Low	375	47	52	46	40	34	25	24

FL SOUND DATA

NOTES:

1. Sound data tested in accordance with AHRI 350-2000.

2. Sound levels are expressed in decibels, dB RE: 1 x 10-12 Watts.


3. Total sound power level data based on both exposed cabinet and concealed models with fan CFM at corresponding motor tap with 115/1/60 Volt motor, 3 row coil, 1" throwaway filter, 0.0" external static pressure and standard rated internal pressure losses.

MODEL FWC CONCEALED UNIT

Drawings are not to scale and not for submittal or installation purposes.

- 1. All dimensions are in inches [millimeters]. All dimensions are 1/4" [6mm]. Metric vales are soft conversion.
- Junction box size and location varies w/unit features. Control options may be limited. Provide sufficient clearance to access electrical controls and comply w/applicable codes and ordinances. Reduced height control enclosure is standard with opposite end coils.
- 3. Right hand coil connection shown. Left hand unit similar but opposite.
- 4. Some piping package options may require extended drain pans.
- 5. Size 02 and 03 Models with 208/230vac or 277vac have 3 5/8" [92] extended control enclosure.

	DIMEN	SIONS	
UNIT MODEL	A	В	С
FWC02	23 3/16 [589]	22 3/4 [578]	16" [406]
FWC03	27 3/16 [691]	26 3/4 [679]	20" [508]
FWC04	33 3/16 [843]	32 3/4 [832]	26" [660]
FWC06	43 3/16 [1097]	42 3/4 [1086]	36" [914]
FWC08	45 3/16 [1148]	44 3/4 [1137]	38" [965]
FWC10	59 3/16 [1503]	58 3/4 [1492]	52" [1320]
FWC12	67 3/16 [1707]	66 3/4 [1695]	60" [1524]




MODEL FWX EXPOSED UNIT

Drawings are not to scale and not for submittal or installation purposes.

- 1. All dimensions are Inches [millimeters]. All dimensions are $\pm 1/4$ " [6mm]. Metric values are soft conversion.
- 2. Junction box size and location varies with unit features. Control options may be limited. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances.
- 3. Standard cabinet finish is "Pearl White Satin".
- 4. Parametric design available to increase Height or Width. (See parametric offerings drawing.)
- Some control or piping package options may require extended end pockets and/or extended drain pans. (See extended end pocket drawing.)
- 6. False back extension available.

UNIT MODEL	DIM A	DIM B	DIM C	DIM D
02	41 [1041]	22 [559]	19 1/2 [495]	22 3/4 [578]
03	45 [1143]	26 [660]	23 1/2 [597]	26 3/4 [679]
04	51 [1295]	32 [813]	27 1/2 [699]	32 3/4 [832]
06	61 [1549]	42 [1067]	39 1/2 [1003]	42 3/4 [1086]
08	63 [1600]	44 [1118]	39 1/2 [1003]	44 3/4 [1137]
10	77 [1956]	58 [1473]	55 1/2 [1410]	58 3/4 [1492]
12	85 [2159]	66 [1676]	63 1/2 [1613]	66 3/4 [1695]




MODEL FWI SLOPE TOP UNIT


Drawings are not to scale and not for submittal or installation purposes.

- 1. All dimensions are Inches [millimeters]. All dimensions are $\pm 1/4$ " [6mm]. Metric values are soft conversion.
- Junction box size and location varies with unit features. Control options may be limited. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances.
- 3. Standard cabinet finish is "Pearl White Satin".
- 4. Right hand unit shown, left hand unit similar, but opposite.
- 5. Parametric design available to increase Height or Width. (See parametric offerings drawing.)
- Some control or piping package options may require extended end pockets and/or extended drain pans. (See extended end pocket drawing.)
- 7. False back extension available.

UNIT MODEL	DIM A	DIM B	DIM C	DIM D
02	41 [1041]	22 [559]	19 1/2 [495]	22 3/4 [578]
03	45 [1143]	26 [660]	23 1/2 [597]	26 3/4 [679]
04	51 [1295]	32 [813]	27 1/2 [699]	32 3/4 [832]
06	61 [1549]	42 [1067]	39 1/2 [1003]	42 3/4 [1086]
08	63 [1600]	44 [1118]	39 1/2 [1003]	44 3/4 [1137]
10	77 [1956]	58 [1473]	55 1/2 [1410]	58 3/4 [1492]
12	85 [2159]	66 [1676]	63 1/2 [1613]	66 3/4 1695]



MODEL FWI PARAMETRIC INCREMENTS




	DIMENSION A (inches)												
SIZE	X=0	X=1	X=2	X=3	X=4	X=5	X=6	X=7	X=8	X=9	X=10	X=11	X=12
02	41	42	43	44	45	46	47	48	49	50	51	52	53
03	45	46	47	48	49	50	51	52	53	54	55	56	57
04	51	52	53	54	55	56	57	58	59	60	61	62	63
06	61	62	63	64	65	66	67	68	69	70	71	72	73
08	63	64	65	66	67	68	69	70	71	72	73	74	75
10	77	78	79	80	81	82	83	84	85	86	87	88	89
12	85	86	87	88	89	90	91	92	93	94	95	N/A	N/A
					DIM	ENSION	B (inch	es)					
ALL SIZES	Y=0	Y=1	Y=2	Y=3	Y=4	Y=5	Y=6	Y=7	Y=8	Y=9	Y=10	Y=11	Y=12
	28 3/4	29 3/4	30 3/4	31 3/4	32 3/4	33 3/4	34 3/4	35 3/4	36 3/4	37 3/4	38 3/4	39 3/4	40 3/4

					DIMEN	SION A	(millime	eters)					
SIZE	X=0	X=25	X=51	X=76	X=102	X=127	X=152	X=178	X=203	X=229	X=254	X=279	X=305
02	1041	1067	1092	1118	1143	1168	1194	1219	1245	1270	1295	1321	1346
03	1143	1168	1194	1219	1245	1270	1295	1321	1346	1372	1397	1422	1448
04	1295	1321	1346	1372	1397	1422	1448	1473	1499	1524	1549	1575	1600
06	1549	1575	1600	1626	1651	1676	1702	1727	1753	1778	1803	1829	1854
08	1600	1626	1651	1676	1702	1727	1753	1778	1803	1829	1854	1880	1905
10	1956	1981	2007	2032	2057	2083	2108	2134	2159	2184	2210	2235	2261
12	2159	2184	2210	2235	2261	2286	2311	2337	2362	2388	2413	N/A	N/A
					DIMEN	SION B	(millime	eters)					
ALL SIZES	Y=0	Y=25	Y=51	Y=76	Y=102	Y=127	Y=152	Y=178	Y=203	Y=229	Y=254	Y=279	Y=305
ALL SIZES	730	756	781	806	832	857	883	908	933	959	984	1010	1035

NOTE:

Internal chassis and air openings remain the same. External cabinet can increase in height and width in 1" (25.4mm) increments up to 12" (305mm).

MODEL FWX PARAMETRIC INCREMENTS




					DIM	ENSION	A (inch	es)					
SIZE	X=0	X=1	X=2	X=3	X=4	X=5	X=6	X=7	X=8	X=9	X=10	X=11	X=12
02	41	42	43	44	45	46	47	48	49	50	51	52	53
03	45	46	47	48	49	50	51	52	53	54	55	56	57
04	51	52	53	54	55	56	57	58	59	60	61	62	63
06	61	62	63	64	65	66	67	68	69	70	71	72	73
08	63	64	65	66	67	68	69	70	71	72	73	74	75
10	77	78	79	80	81	82	83	84	85	86	87	88	89
12	85	86	87	88	89	90	91	92	93	94	95	N/A	N/A
					DIM	ENSION	B (inch	es)					
ALL SIZES	Y=0	Y=1	Y=2	Y=3	Y=4	Y=5	Y=6	Y=7	Y=8	Y=9	Y=10	Y=11	Y=12
	25 1/4	26 1/4	27 1/4	28 1/4	29 1/4	30 1/4	31 1/4	32 1/4	33 1/4	34 1/4	35 1/4	36 1/4	37 1/4

	DIMENSION A (millimeters)													
SIZE	X=0	X=25	X=51	X=76	X=102	X=127	X=152	X=178	X=203	X=229	X=254	X=279	X=305	
02	1041	1067	1092	1118	1143	1168	1194	1219	1245	1270	1295	1321	1346	
03	1143	1168	1194	1219	1245	1270	1295	1321	1346	1372	1397	1422	1448	
04	1295	1321	1346	1372	1397	1422	1448	1473	1499	1524	1549	1575	1600	
06	1549	1575	1600	1626	1651	1676	1702	1727	1753	1778	1803	1829	1854	
08	1600	1626	1651	1676	1702	1727	1753	1778	1803	1829	1854	1880	1905	
10	1956	1981	2007	2032	2057	2083	2108	2134	2159	2184	2210	2235	2261	
12	2159	2184	2210	2235	2261	2286	2311	2337	2362	2388	2413	N/A	N/A	
					DIMEN	SION B	(millime	eters)						
ALL SIZES	Y=0	Y=25	Y=51	Y=76	Y=102	Y=127	Y=152	Y=178	Y=203	Y=229	Y=254	Y=279	Y=305	
ALL SIZES	641	667	692	718	743	768	794	819	845	870	895	921	946	

NOTE:


Internal chassis and air openings remain the same. External cabinet can increase in height and width in 1" (25.4mm) increments up to 12" (305mm).



OUTSIDE AIR DAMPER

	DIMENSION	S - In [mm]	
UNIT SIZE	A	В	C
02	22 [559]	8 [203]	7 [178]
03	26 [660]	10 [254]	8 [203]
04	32 [813]	12 [305]	10 [254]
06	42 [1067]	14 [356]	14 [356]
08	44 [1118]	18 [457]	13 [330]
10	58 [1473]	27 [686]	15 1/2 [394]
12	66 [1676]	27 [686]	19 1/2 [495]

- 1. All dimensions are inches [millimeters]. All dimensions are ± 1/4" [6mm]. Metric values are soft conversion.
- 2. Model FWC shown; typical for Models FWX and FWI.
- 3. The standard damper options may not provide freeze protection under all conditions and applications. Other forms of freeze protection may be required.
- 4. Right hand unit shown; left hand unit is similar but opposite.




NOTES:

1. Material is .050" aluminum.

2. Wall box should be installed pitched slightly toward exterior surface of wall.


3. "Weep" holes should not be obstructed when sealing box to the wall.

RETURN AIR TOE KICK




DIM A 22 3/4 [578]
26 3/4 [679]
32 3/4 [832]
42 3/4 [1086]
44 3/4 [1137]
58 3/4 [1492]
66 3/4 [1695]

- 1. All dimensions are inches [millimeters]. All dimensions are ± 1/4" [6mm]. Metric values are soft conversion.
- 2. Typical for FWX or FWI models.
- 3. Return grille is held in place with sheet metal screws.



UNIT	DIMENSION									
SIZE		Α		В	С					
02	23"	[584]	22"	[559]	17"	[432]				
03	28"	[711]	27"	[686]	22"	[559]				
04	36"	[914]	35"	[889]	30"	[762]				
06	50"	[1270]	49"	[1245]	44"	[1118]				




NOTES:

- 1. All dimensions are inches [mm] and are ± 1/4" [6mm]. Metric values are soft conversion.
- 2. Junction box size and location varies with unit features. Control options may be limited. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances.
- 3. Left hand unit shown; right hand unit similar but opposite.
- 4. Auxiliary drain pan ships loose for field installation.

MODEL FLX EXPOSED CABINET

MODEL FLC CONCEALED




NOTES:

1. See notes 1, 2 and 3 above.

2. Standard cabinet finish is Pearl White Satin.

UNIT	DIMENSION				
SIZE	Α		В		
02	41"	[1041]	19 1/2"	[495]	
03	46"	[1168]	23 1/2"	[597]	
04	54"	[1372]	31 1/2"	[800]	
06	68"	[1727]	43 1/2"	[1105]	



PIPING PACKAGES

All the packages and components described in this brochure are optional, extra cost features. Consult your Johnson Controls sales representative for details. Not all components are available on all unit models. See valve package code charts.

All standard valve packages and piping components described in this catalog are for chilled and hot water applications. They may also be used with ethylene and propylene glycol solutions up to 50% concentration.

FW and FL fan coil unit packages are factory assembled and shipped loose for field installation and wiring.

FW and FL unit valve packages are designed to mount directly onto the coil connections.

Control valve actuators are removable, and may be serviced or replaced without removal of the valve body.

Control valves are piped normally closed to the coil. Control valves are available normally open.

3-Way control valves are piped as mixing valves.

All ball isolation valves are furnished with an adjustable memory stop feature and may be used as a balancing valve.

Optional unions are installed at the water coil, and are available on VAV products, and all fan coil units except VH. Unions must be ordered on both coils of 4-pipe units. Unions are not available separately.

Pressure/temperature (P/T) ports are located to monitor the pressure and temperature across the coil.

Automatic fixed flow controls (FC, FCN, FCS) are available in flow (GPM) ratings as follows:

	Flow Rating	Increment	
1/2"	0.5 - 4.0 GPM	0.5 GPM	
	>4.0 - 6.0 GPM	1.0 GPM	

Individual coil GPM requirements must be specified at time of order. FC = 2-8 psig AFS.

CONTROL DEVICE LEGEND

MANUAL BALL VALVE WITH MEMORY STOP (BVMS)			3-WAY CONTROL VALVE
FIXED FLOW CONTROL VALVE (FC)	FC	AUTOMATIC CARTRIDGE FLOWFCN	AUTOMATIC CARTRIDGE FLOWFCS
ADJUSTABLE FLOW CIRCUIT SETTER (AFS)	— <u>ř</u> ř—	BYPASS BALANCE VALVE (BPV)	PRESSURE-TEMPERATURE
Y-STRAINER (Y-STR)	—Ų—	Y-STRAINER W/CLEANOUT	UNION
FLEXIBLE HOSE (FH)	\sim		SCHRADER FITTING



Valve and component performance ratings shown are maximum values. Appearance and actual ratings may vary with component size.

Adjustable flow setter (AFS) is rated for full shut-off and replaces the return line ball isolation valve on all products except the VH fan coil unit.

2-Pipe "change-over" units using a 2-way control valve and factory thermostat must be ordered with a $\frac{1}{4}$ " "bleed" line to assure proper changeover thermostat (aquastat) operation. The $\frac{1}{4}$ " "bleed" line is optional on 2-pipe "changeover" units with field provided thermostats.

Some piping packages may require extended end pocket with extended auxiliary drain pan. Requirements for field furnished and installed valve package and piping insulation must be determined by others on an individual application basis.

Actuators supplied with factory mounted piping packages include color coded plug and play connections with insulated wire to connect to relay board.

The valve package piping and component details shown in this catalog are for standard valves and components. The suitability of all valve packages and components must be determined by others based on individual application requirements. Johnson Controls assumes no responsibility for selection and/ or application of valve packages and components.

Modulating cooling valve control can increase part load space relative humidity. Johnson Controls does not encourage or endorse modulating valve control for fan coil cooling systems, and is not liable for high humidity problems that may result. Modulating heating valve control may result in low leaving air temperatures while the valve reduces flow and as setpoint is approached.

Contact the factory for any requirements not shown in this catalog.


2-WAY PIPING PACKAGE												
Package	C	omponen	ts	Valve Size		Unions		P/T	1/4" Bleed	Y-STR w/		
Code	BVMS	FC	AFS	1/2"	3/4"	1"*	1/2"	3/4"	1"*	Ports	Line	BDV
24	Х									х	х	х
25	Х	х		х	х	х	х	х	х	х	х	х
29	Х		Х							Х	х	х

Code 24 2-Way Control Valve and Ball Valves With Memory Stop


Code 25 2-Way Control Valve, Ball Valves with Memory Stop, and Fixed Flow Control

Code 29 2-Way Control Valve, Ball Valve with Memory Stop, and Adjustable Flow Setter


3-WAY PIPING PACKAGE											
Package	Package Components			Valve Size		Unions		P/T Ports	Y-STR w/		
Code	BVMS	FC	AFS	1/2"	3/4"	1"*	1/2"	3/4"	1"*	F/T FUILS	BDV
36	х									х	х
37	х	х		х	х	х	х	х	х	х	х
41	х		х							х	х



Code 36 3-Way Control Valve and Ball Valves With Memory Stop




Code 37 3-Way Control Valve, Ball Valves with Memory Stop, and Fixed Flow Control



Code 41 3-Way Control Valve, Ball Valve With Memory Stop, and Adjustable Flow Setter

3-WAY PACKAGE WITH BALANCE BYPASS VALVE										
Package	Components			Valve Size			Unions			D/T Dorto
Code	BVMS	FC	AFS	1/2"	3/4"	1"*	1/2"	3/4"	1"*	P/T Ports
50	х			v	v	v	v	v	v	Х
53	х		Х	~	X	X	х	×	×	Х



Code 50 3-Way Control Valve, Ball Valve in Bypass, and Ball Valves With Memory Stop

LEGEND, COMPONENT PRESSURE RATINGS

BVMS:	Manual Ball Valves w/Memory Stop, 600 PSIG
FC:	Fixed Flow Control, 500 PSIG
AFS	Adjustable Flow Circuit Setter, 300 PSIG
P/T Port:	Pressure/Temperature Test Port, 400 PSIG
Union:	125 PSIG (contact factory for 600 PSIG)
Control Valve:	300 PSIG
BPV:	Balance Bypass Valve, 400 PSIG
Y-STR:	Y-Strainer
BDV:	Blow Down Valve

NOTES:

COL

Code 53

3-Way Control Valve, Ball Valve in Bypass, Ball Valve With Memory Stop, and Adjustable Flow Setter

- All drawings subject to change without prior notice.
- 2. Diagrams show component position in relation to fluid flow. Actual valve package configuration varies with unit type, hand connection, and pipe size.
- 3. 1/4" bleed line is required on 2-pipe cool and heat auto changeover systems with factory provided thermostats; optional for thermostats by others.
- 4. Unions provided as standard on all FW piping packages.

4.0.0.2


. -

<u>v</u> ...

Valve close off pressure

Ш X





PIPING PACKAGES



Manual Ball Valve w/Memory Stop (BVMS)

An adjustable stop position lever to limit travel of the On/Off handle. This allows the ball valve to be closed, and returned to the balance setting position without re-testing the system. 1/2" size shown.

Nominal Size:	1/2"	3/4"	1"
Body Material:	Brass	Brass	Brass
Ball: F	lard Chrome	Hard Chrome	Hard Chrome
	Plated	Plated	Plated
Seats:	Teflon	Teflon	Teflon
Stem Seal: (2)	Viton O-Rings	Teflon	Teflon
Connection:	Sweat	Sweat	Sweat
Pressure Rating	600	600	600
(psig):			
Temp. Rating, °I	-: 325	325	325
Cv:	17	32	27



Flexible Hose Kits, 18" (FH)

Materials:

Flow Rates:

Pressure Temp. Rating (450 PSIG test pressure) Minimum Burst Pressure: Flame Spread: Smoke Development: Ball Valve w/Memory Stop: Ball: Seats: Stem Seal: Pressure Rating: Temperature Rating: Cv: EPDM inner lined, KeFLar® reinforced hose with stainless steel outer covering 0.5 to 12.0 GPM, based on application 375 PSIG @ 250°F

1500 PSI Not greater than 25 per UL 723 Not greater than 50 per UL 723 Full port brass Stainless steel Teflon (2) Viton O-Rings 600 PSIG WOG 325°F 20

Available in 1/2" size only.



Typical 2-Way, 2-Position Control Valve

A2-position water control valve driven open with spring return upon a call for heating or cooling to maintain space temperature. In open position, water can flow through the unit's water coil to heat or cool the space depending on supply water temperature. In closed position, water cannot flow through the water coil. Control valves are piped normally closed to the coil as standard. Valve actuators can be line or low (24VAC) voltage.

Nominal Size	1/2" 2-Way	3/4" 2-Way	1" 2-Way
Body Material:	Brass	Brass	Brass
Connection:	Sweat	Sweat	Sweat
Pressure Rating (psig):	300	300	300
Temperature Rating, °F	: 200	200	200
Cv:	2.5	5.0	8.0
Maximum Close-off			
Pressure, Std. (PSIG)): 40	20	17
High Close-off:	50	25	20
Power Consumption:	7VA	7VA	7VA



Typical 3-Way, 2-Position Control Valve

A 2-position water control valve driven open with spring return (bypass) upon a call for heating or cooling to maintain space temperature. Energized, the bypass port is blocked, and water can flow through the unit's water coil to heat or cool the space depending on the supply water temperature. De-energized, water cannot flow through the water coil but is forced to flow through the bypass port, bypassing the coil. Control valves are piped normally closed to the coil as standard (in full bycan be line or low (24)/(AC)

pass). valve actuators of	can be line of	10W (24VAC)	vollage.
Nominal Size	1/2" 3-Way	3/4" 3-Way	1" 3-Way
Body Material:	Brass	Brass	Brass
Connection:	Sweat	Sweat	Sweat
Pressure Rating (psig):	300	300	300
Temperature Rating, °F	: 200	200	200
Cv:	3.0	5.0	8.0
Maximum Close-off			
Pressure (PSIG):	N/A	N/A	N/A
Power Consumption:	7VA	7VA	7VA

Typical 2-Way Modulating Control Valve

A 3-wire floating point, fail-in-place (non-spring return) modu-lating water control valve, driven open or closed upon a call for heating or cooling to maintain space temperature. In the open position, water can flow through the unit's water coil to heat or cool the space depending on supply water temperature. In the closed position, water cannot flow through the wa-ter coil. Factory furnished 2-way valve packages are piped normally closed to the water coil. The floating point control valve is compatible with any 24VAC three-wire signal when three minute time-out logic resides in the thermostat or system controller

Nominal Size	1/2" 2-Way	3/4" 2-Way	1" 2-Way	
Body Material:	Brass	Brass	Brass	
Connection:	Sweat	Sweat	Sweat	
Pressure Rating (psig):	300	300	300	
Temperature Rating, °F:	200	200	200	
Cv:	2.0	4.0	8.0	
Maximum Close-off Pres	ssure			
Operating Mode:	50	35	35	
Power Consumption:	1VA	1VA	1VA	
Contact factory for 3-wir	e floating, sp	oring return ap	plications.	




Typical 3-Way Modulating Control Valve A 3-wire floating point, fail-in-place (non-spring return) modulating water control valve, driven open or closed (bypass) upon a call for heating or cooling to maintain space temperature. In the "open" position, the bypass port is closed and water is directed through the unit's water coil to heat or cool the space depending on supply water temperature. In the "closed" position, the service (water coil) port is closed and water is directed through the bypass port. Factory furnished 3-way valve packages are piped as "mixing" valves. The floating point control valve is compatible with any 24VAC three-wire signal when three minute time-out logic resides in the thermostat or system controller

the thermostal of system	11 001101010	· · ·	
Nominal Size	1/2" 3-Wa	y 3/4" 3-Way	1" 3-Way
Body Material:	Brass	Brass	Brass
Connection:	Sweat	Sweat	Sweat
Pressure Rating (psig):	300	300	300
Temperature Rating, °F	: 200	200	200
Cv:	2.0	4.0	8.0
Maximum Close-off Pre	ssure		
Operating Mode:	N/A	N/A	N/A
Power Consumption:	1VA	1VA	1VA
Contact factory for 3-will	re floating	spring return a	oplications

Contact factory for 3-wire floating, spring return applications.





Automatic Fixed Flow Control (FC)

A pressure compensated automatic fixed flow control device designed to limit the flow GPM through the unit coil. Desired GPM must be specified when ordering. Device A shown is typical for controlling flow up to 8.0 GPM, and features a changeable flow cartridge. Devide B is typical for flows above 8.0 GPM.

Nominal Size (A): Nominal Size (B): Body Material: Connection: Pressure Rating (psig) (A): Pressure Rating (psig) (B): Temp. Rating, °F: Cv:

1/2" and 3/4" 3/4" and 1" Copper Sweat 600 522 220 Variable With Inlet Pressure



Automatic Cartridge Flow Control (FCN, FCS)

An automatic fixed flow control device with a replaceable stainless steel cartridge, and two pressure/temperature ports, designed to limit the flow GPM through the unit coil to ±5% of rated GPM. Desired GPM must be specified when ordering. Available with 20 mesh stainless steel screen. 1/2" size shown.

Nominal Size: 1/2", 3/4", and 1" Body Material: Connection: Seals: Pressure Rating (psig): 230 Temp. Rating, °F: PSIG Range:

Forged brass Sweat **EPDM O-Rings** 250 2 - 32

Optional Strainer: Body Material:

20 mesh stainless steel*

* The optional strainer is internal and does not affect the dimensions.



Adjustable Flow Circuit Setter (AFS)

A control device designed to allow maximum water flow through the unit coil in the Open (0%) position, and as little as 10% of flow through the unit coil in the Closed (90%) position. The device has a calibrated nameplate, built in test ports and adjustable mechanical stops, and is suitable for positive shutoff.

Nominal Size: Body Material: Connection: Pressure Rating (psig): Temp. Rating, °F: Cv:

1/2", 3/4", and 1" Bronze Sweat 300 250 Variable



Balance Bypass Valve (BPV)

A plug type valve designed to balance the water flow through the bypass circuit of a 3-way control valve. Manual adjustment is required. No calibration is provided at the valve.

Nominal Size: Body Material: Connection: Pressure Rating (psig): Temp. Rating, °F: Cv: 1/2", 3/4", and 1" Bronze Sweat 400 200 Adjustable



Unions

A fitting used to provide a mechanical connection between the coil and valve package that can be connected, disconnected, and re-connected without the need to cut tubing or unsolder a joint. Unions are installed at the coil on HL, HP, and FW fan coil units. Unions are not available on VH fan coil units.

Nominal Size: Body Material: Connection: Pressure Rating (psig): Temp. Rating, °F: 1/2", 3/4", and 1" Bronze/Copper Sweat 500 200

*Contact factory for unions rated at 600 PSIG and 325°F.



Y-Strainer (Y-STR)

Designed to allow water to flow through a built in screen to filter debris or contaminates from the water system. With the water system isolated, the plug can be removed from the blowdown leg of the strainer and the captured debris removed from the screen. After the plug is replaced, the system can be put back in operation and the strainer will continue to filter the unit's water.

Nominal Size: Body Material: Connection: Pressure Rating (psig): Temp. Rating, °F: Screen: 1/2" and 3/4" Forged Brass Sweat 600 325 20 Mesh Stainless Steel



Blow Down Valve (BDV)

A standard ball valve installed on the strainer blowdown leg to allow flushing the strainer screen without removing the plug in the blowdown leg. This valve has a standard ½" garden hose connection to allow fluid to be piped to a container or remote location during cleaning. Not available separately.

Nominal Size:	1/4"
Body Material:	Bronze
Connection:	MPT
Pressure Rating (psig):	600
Temp. Rating, °F:	200



Optional Pressure/Temperature

Test Port Locations (P/T)

Designed to allow testing of water pressure, differential pressure or water temperature without interrupting the waterside operation of the Fan Coil Unit. Sensor probes (1/8") are not included.

Nominal Size:	1/4"
Body Material:	Brass
Connection:	MPT
Pressure Rating (psig):	400
Temp. Rating, °F:	250



Aqua Thermostat

The aqua thermostat, also called an automatic seasonal changeover switch or aquastat, is a switch designed to change a room thermostat from heating to cooling and back, based on the temperature of the water supplied to a 2-pipe unit to be used for both heating and cooling. The switch is shipped loose and is mounted in the field on the water tubing using the integral clip or spring.

)
,
,
,
)

GUIDE SPECIFICATIONS: FW AND FL SERIES

GENERAL

Furnish and install Johnson Controls Vertical Floor Direct Drive Fan Coil Units where indicated on the plans and in the specifications. All units shall be capable of meeting or exceeding the scheduled capacities for cooling, heating and air delivery. Units shall be ETL listed in compliance with UL/ANSI Standard 1995, and be certified as complying with AHRI Standard 440-2008.

CONSTRUCTION

All unit chassis shall be fabricated of heavy gauge galvanized steel panels able to meet 125 hour salt spray test per ASTM B-117. All unit chassis panels shall be insulated with Elastomeric Closed Cell Foam Insulation. Insulation shall conform to UL 181 for erosion and NFPA 90A for fire, smoke and melting, and comply with a 25/50 Flame Spread and Smoke Developed Index per ASTM E-84 or UL 723. Additionally, insulation shall comply with Antimicrobial Performance Rating of 0, no observed growth, per ASTM G-21. Polyethylene or Fiberglass insulation is not acceptable.

All exposed units shall have exterior panels fabricated of not less than 20 gauge galvannealed steel [Provide a 16 gauge front panel on exposed units]. The front panel shall be attached with quarter turn quick open fasteners to allow for easy removal and access for service. [The front panel shall be attached with tamper proof fasteners. Side panels shall be removable for access to controls and piping within the end pockets].

Top panel shall be removable from fan coil without the need to disconnect piping or electrical wiring (FWX/FWI). The top panel shall be removed through not more than 8 screws.

Provide a grille in the return air opening (FLX only). [Provide a grille in the return air opening. (FWX, FWI).] [Provide a decorative return air opening (FWC).]

All exposed units shall include a recessed stamped louver discharge grille. Louver discharge grille shall be reverse stamped (FWI only). [Provide an architectural grade linear bar discharge grille with a powder coated paint finish to match cabinet color. Liquid coat paint shall not be acceptable.]

All concealed units shall have a minimum 1" duct collar on the discharge.

PAINTED FINISH

All painted cabinet exterior panels shall be finished with a heat cured anodic acrylic powder paint of the standard factory color. Liquid coat paint shall not be acceptable.

SOUND

Units shall have published sound power level data tested in accordance with AHRI Standard 350.

POWER

Units shall not exceed scheduled power consumption.

FAN & MOTOR

Unit fan shall be dynamically balanced, forward curved, DWDI centrifugal type constructed of galvanized steel for corrosion resistance. Motors shall be high efficiency, permanently lubricated sleeve bearing, permanent splitcapacitor type with UL and CSA listed automatic reset thermal overload protection and three separate horsepower taps. Shaded pole motors are not acceptable. Single speed motors are not acceptable.

[Provide Electronically Commutated (EC) Motor capable of operation with low voltage 3 speed thermostat. Motor shall come factory programmed and configured for 3 speed operation. Each speed shall be manually adjustable in the field. All manual speed adjustments shall be stored in non-volatile memory. Motor shall be capable of accepting a 2-10 VDC output from BAS. Motor bearings shall be rated for L10-40,000 hours.]

The fan/motor assembly shall be removable and serviceable through the front panel. Each fan/motor assembly shall be fastened by no more than 2 screws. The fan/ motor assembly shall be no longer than 44", and shall be easily removable by a single service technician. The motors shall have quick connectors to allow service and removal without the need for tools.

DRAIN PAN

Primary condensate drain pans shall be single wall, heavy gauge galvanized steel for corrosion resistance, and extend under the entire coil section. Drain pans shall be of one piece construction and be positively sloped for condensate removal. Drain pan access that requires removal of coils is not acceptable.

The primary drain pan shall be externally insulated with a fire retardant, elastomeric closed cell foam insulation. The insulation shall carry no more than a 25/50 Flame Spread and Smoke Developed Rating per ASTM E-84 and UL 723 and an Antimicrobial Performance Rating of 0, no observed growth, per ASTM G-21. Double wall non-corrosive auxiliary drain pan is used for condensate from primary drain pan and optional valve packages.

Option: Provide a primary drain pan constructed entirely of heavy gauge stainless steel for superior corrosion resistance.

GUIDE SPECIFICATIONS: FW AND FL SERIES

COILS

All cooling and heating coils shall optimize rows to meet the specified capacity. Coils shall have seamless copper tubes and shall be mechanically expanded to provide an efficient, permanent bond between the tube and fin. Minimum copper tube thickness shall be .016" [.025"].

Fins shall have high efficiency aluminum [copper] surface optimized for heat transfer, air pressure drop and carryover. Lanced fins shall not be acceptable.

All coils shall be tested at 325 PSIG air pressure under water, and rated for a maximum 300 PSIG working pressure at 200°F. Coils shall be circuited for counter flow to maximize unit efficiency.

All water coils shall be designed to connect with ½" nominal pipe connections.

Coil Casing shall be fabricated from galvanized steel [stainless steel].

Heating coils shall be furnished in the pre-heat (FW Only) or re-heat position.

Direct expansion cooling coils shall be factory sealed and charged with minimum 25 PSIG nitrogen or refrigerated dry air.

Steam coils shall be standard single tube steam type suitable for temperatures above 35°F and 15 PSIG steam pressure.

All water coils shall be provided with a manual air vent fitting to allow for coil venting.

FILTERS

All units shall be furnished with a minimum 1" nominal glass fiber throwaway (1" pleated MERV 7) (1" pleated MERV 8) (1" pleated MERV 13) filter. Filters shall be tight fitting to prevent air bypass. Filters shall be easily removable from the return air opening without the need for tools (FW Only).

ELECTRICAL

Units shall be furnished with single point power connection. Provide an electrical junction box for motor and other electrical terminations.

Option: Provide 24 VAC fan relay board with 25 VA transformer. Fan relay board designed to operate in conjunction with factory provided (field provided) 24 V thermostat. Fan relay board designed to accept 115, 208, 220, 230, or 277 V input power. Fan relay board to be factory installed.

Relay board shall operate with generic thermostat designed to control up to three independently energized fan speeds.

ELECTRIC HEAT

Furnish an electric resistance heating assembly as an integral part of the fan coil unit, with the heating capacity, voltage and kilowatts scheduled. The heater assembly shall be rated for installation on the fan coil unit and be located so as not to expose the fan assembly to excessive leaving air temperatures that could affect motor performance.

The heater and unit assembly shall be listed for zero clearance and meet all NEC requirements, and be ETL listed with the unit as an assembly in compliance with UL/ANSI Standard 1995.

All heating elements on floor mounted units shall be finned tubular type. Elements shall be constructed of nickel chromium resistance wire centered in tubes and embedded in refractory material. Terminals shall be sealed with silicone rubber to protect against moisture. Terminals and hardware shall be stainless steel for corrosion resistance. All internal wiring shall be rated for 105°C minimum.

All heaters shall include over temperature protection consisting of an automatic reset primary thermal limit and back-up secondary thermal limit. All heaters shall be single stage.

Option: Devices used to energize and de-energize (switch) electric heat must be totally silent. Magnetic, mercury, and/or quiet relays and/or contactors are not acceptable.

PIPING PACKAGES

Provide a standard factory assembled valve piping pack- age to consist of a 2 or 3-way, on/off, motorized electric control valve and two ball isolation valves.

Control valves shall be piped normally closed to the coil. Control valves shall be wired to relay board through quick connects to allow service and replacement of valves. Quick connects shall prevent incorrect wiring through physical and color coded visual confirmation. Maximum entering water temperature on the control valve shall be 200°F, and maximum operating pressure shall be 300 PSIG.

Unions shall be provided to allow removal of piping package from unit without the need for brazing or cutting pipe.

GUIDE SPECIFICATIONS: FW AND FL SERIES

Option: Provide 3-wire floating point modulating control valve (fail-in-place), in lieu of standard 2-position control valve with factory assembled valve piping package.

Option: Provide high pressure close-off actuator for 2-way on/off control valve. Maximum close-off pressure is 50 PSIG (1/2"), 25 PSIG (3/4)", or 20 PSIG (1").

Option: Provide either a fixed or adjustable flow control device for each piping package.

Option: Provide pressure-temperature ports (P/T) for each piping package to allow measurement across the coil.

Piping packages shall be completely factory assembled, including interconnecting pipe and shipped loose for field installation.

Option: Piping package will be shipped factory installed.

OUTSIDE AIR DAMPER (FW ONLY)

Provide a manual or two position motorized outside air damper integral to the unit.

Option: Provide aluminum outside air wall box (FW Only) with integral insect screen and weep holes for field installation.

Printed on recycled paper

